

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270673

Luminaire Tested: P3A20R559740D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R559740D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2179.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270673

CATALOG NUMBER: P3A20R559740D010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1270673

CATALOG NUMBER: P3A20R559740D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96		94
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94	92	90		89
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90	87	85		84
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		85	83	80		79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82	78	76		74
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78	74	72		70
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74	70	68		66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64		63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68	64	61		60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	604359
5°	598744
10°	622790
15°	614147
20°	566326
25°	460793
30°	279891
35°	96878
40°	27652
45°	13211
50°	5595
55°	2523
60°	2895
65°	2542
70°	2116
75°	2796
80°	2020
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13211 cd/sqm

TEST NUMBER: P1270673

CATALOG NUMBER: P3A20R559740D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.0	12.1
10°-20°	751.9	34.5
20°-30°	838.2	38.5
30°-40°	274.2	12.6
40°-50°	36.2	1.7
50°-60°	7.7	0.4
60°-70°	4.5	0.2
70°-80°	2.8	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1853.1	85.0
0°-40°	2127.3	97.6
0°-60°	2171.1	99.6
0°-90°	2179.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2179.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2756	
5°	2720	263
15°	2705	752
25°	1904	838
35°	362	274
45°	43	36
55°	7	8
65°	5	4
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1270673

CATALOG NUMBER: P3A20R559740D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2756.1
2.5°	2736.4
5°	2720.1
7.5°	2759.4
10°	2797.0
12.5°	2777.4
15°	2705.3
17.5°	2590.7
20°	2426.9
22.5°	2200.9
25°	1904.5
27.5°	1527.9
30°	1105.4
32.5°	678.0
35°	361.9
37.5°	183.4
40°	96.6
42.5°	62.2
45°	42.6
47.5°	29.5
50°	16.4
52.5°	9.8
55°	6.6
57.5°	6.6
60°	6.6
62.5°	4.9
65°	4.9
67.5°	3.3
70°	3.3
72.5°	3.3
75°	3.3
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)