

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268533

Luminaire Tested: P3A02R159740DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R159740DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 245.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268533

CATALOG NUMBER: P3A02R159740DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268533

CATALOG NUMBER: P3A02R159740DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	90	89
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	86	85
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	82	81
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	79	78
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	76	75
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	73	72
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	71	70
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	68	67
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209303
5°	185780
10°	129011
15°	76300
20°	43450
25°	24848
30°	13749
35°	7335
40°	4065
45°	2202
50°	1365
55°	1070
60°	921
65°	882
70°	769
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2202 cd/sqm

TEST NUMBER: P1268533

CATALOG NUMBER: P3A02R159740DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	29.3
10°-20°	94.7	38.7
20°-30°	48.8	19.9
30°-40°	18.3	7.5
40°-50°	6.0	2.4
50°-60°	2.6	1.1
60°-70°	1.6	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.3	87.9
0°-40°	233.6	95.3
0°-60°	242.2	98.8
0°-90°	245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	954	
5°	844	72
15°	336	95
25°	103	49
35°	27	18
45°	7	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268533

CATALOG NUMBER: P3A02R159740DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	954.5
1°	952.6
2°	940.1
3°	916.2
4°	884.8
5°	844.0
6°	797.7
7°	747.0
8°	690.6
9°	634.9
10°	579.4
12.5°	445.8
15°	336.1
17.5°	251.6
20°	186.2
22.5°	139.0
25°	102.7
27.5°	74.8
30°	54.3
32.5°	38.5
35°	27.4
37.5°	19.6
40°	14.2
42.5°	10.1
45°	7.1
47.5°	5.2
50°	4.0
52.5°	3.3
55°	2.8
57.5°	2.4
60°	2.1
62.5°	1.9
65°	1.7
67.5°	1.4
70°	1.2
72.5°	1.2
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)