

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268597

Luminaire Tested: P3A02R259740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R259740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 189.0 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268597

CATALOG NUMBER: P3A02R259740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268597

CATALOG NUMBER: P3A02R259740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44909
5°	43848
10°	40636
15°	36186
20°	31106
25°	26445
30°	21750
35°	16945
40°	12194
45°	7753
50°	4571
55°	3135
60°	2895
65°	2698
70°	2436
75°	2203
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7753 cd/sqm

TEST NUMBER: P1268597

CATALOG NUMBER: P3A02R259740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.5	9.8
10°-20°	44.3	23.4
20°-30°	50.0	26.5
30°-40°	39.5	20.9
40°-50°	20.0	10.6
50°-60°	8.0	4.2
60°-70°	5.1	2.7
70°-80°	2.8	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.7	59.7
0°-40°	152.3	80.6
0°-60°	180.2	95.4
0°-90°	189.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	189.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	205	
5°	199	18
15°	159	44
25°	109	50
35°	63	40
45°	25	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1268597

CATALOG NUMBER: P3A02R259740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	204.8
1°	204.8
2°	204.1
3°	203.0
4°	201.3
5°	199.2
6°	196.6
7°	193.5
8°	190.2
9°	186.5
10°	182.5
11°	178.0
12°	173.8
13°	168.8
14°	164.1
15°	159.4
17.5°	146.2
20°	133.3
22.5°	121.0
25°	109.3
27.5°	97.7
30°	85.9
32.5°	74.9
35°	63.3
37.5°	52.7
40°	42.6
42.5°	33.2
45°	25.0
47.5°	18.6
50°	13.4
52.5°	10.1
55°	8.2
57.5°	7.5
60°	6.6
62.5°	5.9
65°	5.2
67.5°	4.5
70°	3.8
72.5°	3.3
75°	2.6
77.5°	2.1
80°	1.6
82.5°	1.2
85°	0.7
87.5°	0.2



TEST NUMBER: P1268597

CATALOG NUMBER: P3A02R259740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)