

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268634

Luminaire Tested: P3A02R309740DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1268634  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R309740DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 250.0 lumens  
Efficiency: N/A  
Efficacy: 69.5 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268634  
CATALOG NUMBER: P3A02R309740DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1268634

CATALOG NUMBER: P3A02R309740DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	78	75	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	76	72	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	145887
5°	138851
10°	116787
15°	84223
20°	52248
25°	29711
30°	16509
35°	8968
40°	4723
45°	2574
50°	1365
55°	918
60°	833
65°	882
70°	769
75°	593
80°	631
85°	503

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2574 cd/sqm



TEST NUMBER: P1268634  
 CATALOG NUMBER: P3A02R309740DE010 E3DLP1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	22.7
10°-20°	101.0	40.4
20°-30°	58.4	23.3
30°-40°	22.1	8.9
40°-50°	6.8	2.7
50°-60°	2.3	0.9
60°-70°	1.6	0.6
70°-80°	0.8	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.1	86.4
0°-40°	238.3	95.3
0°-60°	247.4	98.9
0°-90°	250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	250.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	665	
5°	631	57
15°	371	101
25°	123	58
35°	34	22
45°	8	7
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1268634  
CATALOG NUMBER: P3A02R309740DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	665.3
1°	664.8
2°	660.8
3°	653.2
4°	643.8
5°	630.8
6°	614.3
7°	595.8
8°	575.3
9°	550.7
10°	524.5
11°	496.2
12°	466.2
13°	434.8
14°	402.9
15°	371.0
17.5°	292.6
20°	223.9
22.5°	166.0
25°	122.8
27.5°	89.3
30°	65.2
32.5°	47.0
35°	33.5
37.5°	23.4
40°	16.5
42.5°	11.6
45°	8.3
47.5°	5.7
50°	4.0
52.5°	2.8
55°	2.4
57.5°	2.1
60°	1.9
62.5°	1.7
65°	1.7
67.5°	1.4
70°	1.2
72.5°	0.9
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0



TEST NUMBER: P1268634  
CATALOG NUMBER: P3A02R309740DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)