

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268976

Luminaire Tested: P3A05R209740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R209740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 187.0 lumens
Efficiency: N/A
Efficacy: 26.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268976
CATALOG NUMBER: P3A05R209740DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1268976

CATALOG NUMBER: P3A05R209740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83				83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76				76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65				65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60				60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55				55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52				52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48				48
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46246
5°	45014
10°	41415
15°	36459
20°	31269
25°	26276
30°	21244
35°	16142
40°	11479
45°	7598
50°	4708
55°	3097
60°	2807
65°	2594
70°	2436
75°	2203
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7598 cd/sqm



TEST NUMBER: P1268976
 CATALOG NUMBER: P3A05R209740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.9	10.1
10°-20°	44.7	23.9
20°-30°	49.6	26.5
30°-40°	37.8	20.2
40°-50°	19.4	10.4
50°-60°	8.0	4.3
60°-70°	5.0	2.7
70°-80°	2.8	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.3	60.6
0°-40°	151.1	80.8
0°-60°	178.5	95.4
0°-90°	187.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	187.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	211	
5°	204	19
15°	161	45
25°	109	50
35°	60	38
45°	24	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1268976
CATALOG NUMBER: P3A05R209740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	210.9
1°	211.2
2°	210.2
3°	209.0
4°	207.1
5°	204.5
6°	201.4
7°	198.1
8°	194.5
9°	190.3
10°	186.0
12.5°	173.6
15°	160.6
17.5°	147.3
20°	134.0
22.5°	120.7
25°	108.6
27.5°	96.4
30°	83.9
32.5°	72.0
35°	60.3
37.5°	50.1
40°	40.1
42.5°	31.6
45°	24.5
47.5°	18.5
50°	13.8
52.5°	10.2
55°	8.1
57.5°	7.4
60°	6.4
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.8
72.5°	3.1
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)