

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269008

Luminaire Tested: P3A05R259740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R259740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 389.1 lumens
Efficiency: N/A
Efficacy: 54.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269008

CATALOG NUMBER: P3A05R259740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269008

CATALOG NUMBER: P3A05R259740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92449
5°	90249
10°	83632
15°	74484
20°	64009
25°	54414
30°	44792
35°	34907
40°	25104
45°	15940
50°	9415
55°	6499
60°	5964
65°	5552
70°	5001
75°	4490
80°	4293
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15940 cd/sqm

TEST NUMBER: P1269008

CATALOG NUMBER: P3A05R259740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.0	9.8
10°-20°	91.1	23.4
20°-30°	102.9	26.5
30°-40°	81.4	20.9
40°-50°	41.1	10.6
50°-60°	16.5	4.2
60°-70°	10.6	2.7
70°-80°	5.8	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.0	59.6
0°-40°	313.4	80.6
0°-60°	371.0	95.4
0°-90°	389.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	389.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	422	
5°	410	38
15°	328	91
25°	225	103
35°	130	81
45°	51	41
55°	17	16
65°	11	11
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1269008

CATALOG NUMBER: P3A05R259740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	421.6
1°	421.6
2°	420.2
3°	417.7
4°	414.3
5°	410.0
6°	404.7
7°	398.4
8°	391.6
9°	383.8
10°	375.6
11°	366.4
12°	357.6
13°	347.5
14°	337.8
15°	328.1
17.5°	300.9
20°	274.3
22.5°	249.1
25°	224.9
27.5°	201.1
30°	176.9
32.5°	154.1
35°	130.4
37.5°	108.6
40°	87.7
42.5°	68.3
45°	51.4
47.5°	38.3
50°	27.6
52.5°	20.8
55°	17.0
57.5°	15.5
60°	13.6
62.5°	12.1
65°	10.7
67.5°	9.2
70°	7.8
72.5°	6.8
75°	5.3
77.5°	4.4
80°	3.4
82.5°	2.4
85°	1.5
87.5°	0.5



TEST NUMBER: P1269008

CATALOG NUMBER: P3A05R259740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)