

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269051

Luminaire Tested: P3A05R359740DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269051
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R359740DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 616.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269051
CATALOG NUMBER: P3A05R359740DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1269051

CATALOG NUMBER: P3A05R359740DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98		96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94		93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90		89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87		86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84		83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81		80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79		77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76		75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74		73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71		70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	401678
5°	393483
10°	366059
15°	268378
20°	137422
25°	49527
30°	19294
35°	6746
40°	2777
45°	744
50°	648
55°	726
60°	658
65°	519
70°	641
75°	847
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 847 cd/sqm



TEST NUMBER: P1269051
 CATALOG NUMBER: P3A05R359740DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.7	27.1
10°-20°	312.7	50.8
20°-30°	110.7	18.0
30°-40°	19.4	3.1
40°-50°	2.8	0.5
50°-60°	1.6	0.3
60°-70°	1.2	0.2
70°-80°	0.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.0	95.8
0°-40°	609.4	98.9
0°-60°	613.8	99.6
0°-90°	616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	616.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1832	
5°	1788	167
15°	1182	313
25°	205	111
35°	25	19
45°	2	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1269051
CATALOG NUMBER: P3A05R359740DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1831.8
1°	1831.3
2°	1825.5
3°	1814.3
4°	1804.1
5°	1787.6
6°	1770.7
7°	1751.7
8°	1728.4
9°	1692.1
10°	1644.0
11°	1577.6
12°	1497.5
13°	1402.5
14°	1297.7
15°	1182.2
17.5°	880.5
20°	588.9
22.5°	355.1
25°	204.7
27.5°	122.2
30°	76.2
32.5°	44.1
35°	25.2
37.5°	16.0
40°	9.7
42.5°	4.9
45°	2.4
47.5°	1.9
50°	1.9
52.5°	1.9
55°	1.9
57.5°	1.5
60°	1.5
62.5°	1.5
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0



TEST NUMBER: P1269051
CATALOG NUMBER: P3A05R359740DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)