

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269136

Luminaire Tested: P3A05R509740DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R509740DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 664.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269136

CATALOG NUMBER: P3A05R509740DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1269136

CATALOG NUMBER: P3A05R509740DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	114	112	109	107		112	109	107	106		105	104	102		102	101	99		98	97	96	95
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91	90
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86	85
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82	80
5	96	89	84	80		94	88	83	79		86	82	79		84	81	78		83	80	77	76
6	92	84	79	75		91	83	79	75		82	78	74		81	77	74		79	76	73	72
7	88	80	75	71		87	79	74	71		78	74	71		77	73	70		76	73	70	69
8	85	76	71	67		83	76	71	67		75	70	67		74	70	67		73	69	66	65
9	81	73	68	64		80	72	67	64		71	67	64		71	66	63		70	66	63	62
10	78	69	64	61		77	69	64	61		68	64	61		68	63	61		67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231253
5°	227118
10°	218077
15°	199956
20°	176322
25°	135153
30°	73480
35°	23637
40°	5553
45°	744
50°	648
55°	726
60°	658
65°	778
70°	641
75°	847
80°	631
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 85°

Luminance: 1258 cd/sqm

TEST NUMBER: P1269136

CATALOG NUMBER: P3A05R509740DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.8	14.6
10°-20°	244.9	36.9
20°-30°	245.2	36.9
30°-40°	68.9	10.4
40°-50°	4.1	0.6
50°-60°	1.6	0.2
60°-70°	1.3	0.2
70°-80°	0.9	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.9	88.4
0°-40°	655.8	98.8
0°-60°	661.5	99.6
0°-90°	664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1055	
5°	1032	97
15°	881	245
25°	559	245
35°	88	69
45°	2	4
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1269136

CATALOG NUMBER: P3A05R509740DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1054.6
2.5°	1049.3
5°	1031.8
7.5°	1008.0
10°	979.4
12.5°	936.2
15°	880.8
17.5°	817.3
20°	755.6
22.5°	679.0
25°	558.6
27.5°	415.9
30°	290.2
32.5°	175.2
35°	88.3
37.5°	41.7
40°	19.4
42.5°	7.3
45°	2.4
47.5°	1.9
50°	1.9
52.5°	1.9
55°	1.9
57.5°	1.5
60°	1.5
62.5°	1.5
65°	1.5
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)