

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269192

Luminaire Tested: P3A05R609740DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R609740DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 627.1 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269192
CATALOG NUMBER: P3A05R609740DE010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1269192
 CATALOG NUMBER: P3A05R609740DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	80	96	89	84	80	87	83	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	68	66				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149725
5°	143781
10°	148049
15°	149944
20°	132405
25°	111587
30°	90495
35°	58946
40°	27079
45°	10389
50°	3480
55°	918
60°	833
65°	778
70°	641
75°	847
80°	631
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10389 cd/sqm



TEST NUMBER: P1269192
 CATALOG NUMBER: P3A05R609740DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	10.0
10°-20°	180.9	28.8
20°-30°	211.0	33.6
30°-40°	136.1	21.7
40°-50°	30.5	4.9
50°-60°	3.0	0.5
60°-70°	1.5	0.2
70°-80°	0.9	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.7	72.5
0°-40°	590.9	94.2
0°-60°	624.4	99.6
0°-90°	627.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	627.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	683	
5°	653	63
15°	660	181
25°	461	211
35°	220	136
45°	34	31
55°	2	3
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1269192
CATALOG NUMBER: P3A05R609740DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	682.8
2.5°	671.6
5°	653.2
7.5°	652.2
10°	664.9
12.5°	673.1
15°	660.5
17.5°	622.7
20°	567.4
22.5°	509.7
25°	461.2
27.5°	413.7
30°	357.4
32.5°	291.4
35°	220.2
37.5°	150.3
40°	94.6
42.5°	56.7
45°	33.5
47.5°	19.4
50°	10.2
52.5°	3.4
55°	2.4
57.5°	1.9
60°	1.9
62.5°	1.5
65°	1.5
67.5°	1.5
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)