

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269321

Luminaire Tested: P3A09R159740DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269321
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R159740DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 437.0 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269321
CATALOG NUMBER: P3A09R159740DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1269321
 CATALOG NUMBER: P3A09R159740DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.1	16.0
10°-20°	129.3	29.6
20°-30°	115.1	26.3
30°-40°	68.1	15.6
40°-50°	28.0	6.4
50°-60°	13.1	3.0
60°-70°	8.0	1.8
70°-80°	4.2	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.6	72.0
0°-40°	382.7	87.6
0°-60°	423.8	97.0
0°-90°	437.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	437.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	859	
5°	791	70
15°	463	129
25°	252	115
35°	106	68
45°	34	28
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1269321
CATALOG NUMBER: P3A09R159740DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	859.4
1°	857.2
2°	850.9
3°	838.1
4°	816.8
5°	791.2
6°	763.6
7°	730.9
8°	696.9
9°	662.1
10°	624.5
12.5°	538.6
15°	462.7
17.5°	397.4
20°	342.8
22.5°	294.5
25°	251.9
27.5°	210.8
30°	172.4
32.5°	137.7
35°	106.4
37.5°	81.6
40°	61.0
42.5°	45.4
45°	34.1
47.5°	26.3
50°	20.6
52.5°	17.0
55°	14.2
57.5°	12.1
60°	10.6
62.5°	9.2
65°	7.8
67.5°	7.1
70°	5.7
72.5°	5.0
75°	4.3
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)