

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269391

Luminaire Tested: P3A09R259740DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R259740DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 742.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269391

CATALOG NUMBER: P3A09R259740DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1269391

CATALOG NUMBER: P3A09R259740DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	89	88
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	85	84
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	81	80
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	77	76
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	74	73
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	71	70
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	65	64
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	475971
5°	444067
10°	355727
15°	241477
20°	146103
25°	85432
30°	48666
35°	26769
40°	14198
45°	7474
50°	4367
55°	3250
60°	2807
65°	2958
70°	2757
75°	2372
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7474 cd/sqm

TEST NUMBER: P1269391

CATALOG NUMBER: P3A09R259740DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	24.1
10°-20°	292.4	39.4
20°-30°	167.1	22.5
30°-40°	65.9	8.9
40°-50°	20.2	2.7
50°-60°	8.0	1.1
60°-70°	5.4	0.7
70°-80°	3.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	638.5	86.1
0°-40°	704.5	94.9
0°-60°	732.7	98.7
0°-90°	742.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	742.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2171	
5°	2017	179
15°	1064	292
25°	353	167
35°	100	66
45°	24	20
55°	8	8
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269391

CATALOG NUMBER: P3A09R259740DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2170.6
1°	2166.3
2°	2148.6
3°	2117.4
4°	2074.1
5°	2017.4
6°	1950.8
7°	1875.6
8°	1788.4
9°	1699.0
10°	1597.6
11°	1497.6
12°	1387.7
13°	1279.2
14°	1167.9
15°	1063.7
17.5°	824.7
20°	626.1
22.5°	470.1
25°	353.1
27.5°	261.7
30°	192.2
32.5°	139.0
35°	100.0
37.5°	70.9
40°	49.6
42.5°	34.0
45°	24.1
47.5°	17.0
50°	12.8
52.5°	9.9
55°	8.5
57.5°	7.8
60°	6.4
62.5°	5.7
65°	5.7
67.5°	5.0
70°	4.3
72.5°	3.5
75°	2.8
77.5°	2.1
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7



TEST NUMBER: P1269391

CATALOG NUMBER: P3A09R259740DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)