

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269424

Luminaire Tested: P3A09R309740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269424
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R309740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 457.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269424

CATALOG NUMBER: P3A09R309740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269424

CATALOG NUMBER: P3A09R309740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156172
5°	151309
10°	136337
15°	112759
20°	87321
25°	65496
30°	47552
35°	31668
40°	19465
45°	11412
50°	7027
55°	5696
60°	4956
65°	4047
70°	3654
75°	3643
80°	2652
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11412 cd/sqm

TEST NUMBER: P1269424

CATALOG NUMBER: P3A09R309740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	13.8
10°-20°	136.8	29.9
20°-30°	124.5	27.2
30°-40°	75.2	16.5
40°-50°	30.2	6.6
50°-60°	13.4	2.9
60°-70°	8.1	1.8
70°-80°	4.4	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.5	71.0
0°-40°	399.8	87.5
0°-60°	443.3	97.0
0°-90°	457.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	457.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	712	
5°	687	63
15°	497	137
25°	271	124
35°	118	75
45°	37	30
55°	15	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1269424

CATALOG NUMBER: P3A09R309740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	712.2
1°	711.5
2°	708.6
3°	703.7
4°	696.6
5°	687.4
6°	676.0
7°	664.0
8°	648.4
9°	630.7
10°	612.3
11°	591.0
12°	568.3
13°	545.6
14°	520.8
15°	496.7
17.5°	433.7
20°	374.2
22.5°	318.9
25°	270.7
27.5°	226.8
30°	187.8
32.5°	151.6
35°	118.3
37.5°	90.7
40°	68.0
42.5°	49.6
45°	36.8
47.5°	27.6
50°	20.6
52.5°	16.3
55°	14.9
57.5°	12.8
60°	11.3
62.5°	9.2
65°	7.8
67.5°	7.1
70°	5.7
72.5°	5.0
75°	4.3
77.5°	3.5
80°	2.1
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1269424
CATALOG NUMBER: P3A09R309740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)