

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269522

Luminaire Tested: P3A09R509740DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269522
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R509740DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 797.0 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269522

CATALOG NUMBER: P3A09R509740DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1269522

CATALOG NUMBER: P3A09R509740DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253752
5°	248646
10°	232884
15°	208492
20°	175459
25°	133895
30°	87026
35°	51584
40°	29827
45°	14947
50°	5561
55°	4320
60°	4035
65°	3684
70°	3654
75°	3643
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 14947 cd/sqm

TEST NUMBER: P1269522

CATALOG NUMBER: P3A09R509740DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.1	13.2
10°-20°	254.0	31.9
20°-30°	249.2	31.3
30°-40°	125.5	15.8
40°-50°	39.7	5.0
50°-60°	10.3	1.3
60°-70°	7.3	0.9
70°-80°	4.5	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.2	76.3
0°-40°	733.7	92.1
0°-60°	783.7	98.3
0°-90°	797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1157	
5°	1130	105
15°	918	254
25°	553	249
35°	193	126
45°	48	40
55°	11	10
65°	7	7
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1269522

CATALOG NUMBER: P3A09R509740DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1157.2
2.5°	1150.1
5°	1129.6
7.5°	1092.7
10°	1045.9
12.5°	985.7
15°	918.4
17.5°	840.4
20°	751.9
22.5°	656.2
25°	553.4
27.5°	444.3
30°	343.7
32.5°	258.7
35°	192.7
37.5°	142.4
40°	104.2
42.5°	73.7
45°	48.2
47.5°	27.6
50°	16.3
52.5°	12.0
55°	11.3
57.5°	9.9
60°	9.2
62.5°	8.5
65°	7.1
67.5°	6.4
70°	5.7
72.5°	5.0
75°	4.3
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)