

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269562

Luminaire Tested: P3A09R559740DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1269562  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R559740DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 253.0 lumens  
Efficiency: N/A  
Efficacy: 22.8 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269562  
CATALOG NUMBER: P3A09R559740DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1269562  
 CATALOG NUMBER: P3A09R559740DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |     |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    | 100 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98  | 97  | 97  | 95  | 94  | 92  |    |    |    | 92  |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 93  | 97  | 93  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |    |    |    | 85  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  | 88  | 84  | 81  | 86  | 83  | 80  | 79  |    |    |    | 79  |
| 4   | 96  | 88  | 82  | 77  | 94  | 87  | 81  | 77  | 84  | 80  | 76  | 82  | 78  | 75  | 80  | 77  | 74  | 73  |    |    |    | 73  |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  | 77  | 73  | 70  | 76  | 72  | 69  | 67  |    |    |    | 67  |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 63  |    |    |    | 63  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  | 69  | 64  | 60  | 68  | 63  | 60  | 59  |    |    |    | 59  |
| 8   | 78  | 68  | 62  | 57  | 76  | 67  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 56  | 55  |    |    |    | 55  |
| 9   | 74  | 64  | 58  | 54  | 73  | 63  | 58  | 54  | 62  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 52  |    |    |    | 52  |
| 10  | 70  | 60  | 55  | 51  | 69  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 54  | 50  | 58  | 53  | 50  | 49  |    |    |    | 49  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 68832 |
| 5°  | 67092 |
| 10° | 62368 |
| 15° | 55551 |
| 20° | 47207 |
| 25° | 38107 |
| 30° | 29042 |
| 35° | 20666 |
| 40° | 13626 |
| 45° | 8094  |
| 50° | 4742  |
| 55° | 2906  |
| 60° | 2588  |
| 65° | 2335  |
| 70° | 1988  |
| 75° | 1779  |
| 80° | 1768  |
| 85° | 1761  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8094 cd/sqm



TEST NUMBER: P1269562  
 CATALOG NUMBER: P3A09R559740DE010 E3DLP1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 28.3   | 11.2      |
| 10°-20°   | 67.8   | 26.8      |
| 20°-30°   | 71.9   | 28.4      |
| 30°-40°   | 48.6   | 19.2      |
| 40°-50°   | 21.3   | 8.4       |
| 50°-60°   | 7.6    | 3.0       |
| 60°-70°   | 4.4    | 1.8       |
| 70°-80°   | 2.3    | 0.9       |
| 80°-90°   | 0.7    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 168.0  | 66.4      |
| 0°-40°    | 216.6  | 85.6      |
| 0°-60°    | 245.5  | 97.0      |
| 0°-90°    | 253.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 253.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 314 |      |
| 5°  | 305 | 28   |
| 15° | 245 | 68   |
| 25° | 158 | 72   |
| 35° | 77  | 49   |
| 45° | 26  | 21   |
| 55° | 8   | 8    |
| 65° | 4   | 4    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1269562  
CATALOG NUMBER: P3A09R559740DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 313.9 |
| 2.5°  | 311.4 |
| 5°    | 304.8 |
| 7.5°  | 294.1 |
| 10°   | 280.1 |
| 12.5° | 263.5 |
| 15°   | 244.7 |
| 17.5° | 223.8 |
| 20°   | 202.3 |
| 22.5° | 179.7 |
| 25°   | 157.5 |
| 27.5° | 135.6 |
| 30°   | 114.7 |
| 32.5° | 94.9  |
| 35°   | 77.2  |
| 37.5° | 61.2  |
| 40°   | 47.6  |
| 42.5° | 35.8  |
| 45°   | 26.1  |
| 47.5° | 19.1  |
| 50°   | 13.9  |
| 52.5° | 9.7   |
| 55°   | 7.6   |
| 57.5° | 7.0   |
| 60°   | 5.9   |
| 62.5° | 5.2   |
| 65°   | 4.5   |
| 67.5° | 3.8   |
| 70°   | 3.1   |
| 72.5° | 2.8   |
| 75°   | 2.1   |
| 77.5° | 1.7   |
| 80°   | 1.4   |
| 82.5° | 1.0   |
| 85°   | 0.7   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)