

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269565

Luminaire Tested: P3A09R559740DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R559740DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 516.0 lumens
Efficiency: N/A
Efficacy: 46.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269565

CATALOG NUMBER: P3A09R559740DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1269565

CATALOG NUMBER: P3A09R559740DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79		
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55		
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52		
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140362
5°	136848
10°	127230
15°	113304
20°	96282
25°	77690
30°	59224
35°	42135
40°	27795
45°	16498
50°	9688
55°	5964
60°	5307
65°	4774
70°	4103
75°	3643
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16498 cd/sqm

TEST NUMBER: P1269565

CATALOG NUMBER: P3A09R559740DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	11.2
10°-20°	138.4	26.8
20°-30°	146.5	28.4
30°-40°	99.0	19.2
40°-50°	43.4	8.4
50°-60°	15.5	3.0
60°-70°	9.1	1.8
70°-80°	4.8	0.9
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	342.6	66.4
0°-40°	441.6	85.6
0°-60°	500.6	97.0
0°-90°	516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	516.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	640	
5°	622	58
15°	499	138
25°	321	147
35°	157	99
45°	53	43
55°	16	16
65°	9	9
75°	4	5
85°	1	2
90°	0	

TEST NUMBER: P1269565

CATALOG NUMBER: P3A09R559740DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	640.1
2.5°	635.2
5°	621.7
7.5°	599.7
10°	571.4
12.5°	537.3
15°	499.1
17.5°	456.5
20°	412.6
22.5°	366.5
25°	321.1
27.5°	276.5
30°	233.9
32.5°	193.5
35°	157.4
37.5°	124.8
40°	97.1
42.5°	73.0
45°	53.2
47.5°	39.0
50°	28.4
52.5°	19.8
55°	15.6
57.5°	14.2
60°	12.1
62.5°	10.6
65°	9.2
67.5°	7.8
70°	6.4
72.5°	5.7
75°	4.3
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)