

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269591

Luminaire Tested: P3A09R609740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R609740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 253.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269591
CATALOG NUMBER: P3A09R609740DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269591

CATALOG NUMBER: P3A09R609740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	67	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64118
5°	62690
10°	58672
15°	52645
20°	45271
25°	37430
30°	29574
35°	21978
40°	15114
45°	9489
50°	5219
55°	3058
60°	2763
65°	2335
70°	1988
75°	2033
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9489 cd/sqm



TEST NUMBER: P1269591
 CATALOG NUMBER: P3A09R609740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	10.5
10°-20°	64.4	25.5
20°-30°	70.6	27.9
30°-40°	51.5	20.3
40°-50°	24.3	9.6
50°-60°	8.0	3.2
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.5	63.9
0°-40°	213.0	84.2
0°-60°	245.3	97.0
0°-90°	253.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	253.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	292	
5°	285	27
15°	232	64
25°	155	71
35°	82	51
45°	31	24
55°	8	8
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1269591
CATALOG NUMBER: P3A09R609740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	292.4
2.5°	290.7
5°	284.8
7.5°	275.7
10°	263.5
12.5°	248.9
15°	231.9
17.5°	213.5
20°	194.0
22.5°	174.2
25°	154.7
27.5°	135.2
30°	116.8
32.5°	99.1
35°	82.1
37.5°	66.8
40°	52.8
42.5°	40.7
45°	30.6
47.5°	22.3
50°	15.3
52.5°	10.1
55°	8.0
57.5°	7.0
60°	6.3
62.5°	5.2
65°	4.5
67.5°	3.8
70°	3.1
72.5°	2.8
75°	2.4
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)