

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273006

Luminaire Tested: P3A02R359830DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1273006  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R359830DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 227.0 lumens  
Efficiency: N/A  
Efficacy: 63.1 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273006

CATALOG NUMBER: P3A02R359830DE010 E3CB1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1273006

CATALOG NUMBER: P3A02R359830DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 103 | 100 | 102 | 100 | 98  |  | 99  | 98  | 96  |  | 97  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 95  | 98  | 96  | 93  |  | 96  | 94  | 92  |  | 94  |
| 4   | 104 | 98  | 94  | 91  | 102 | 97  | 93  | 90  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  |
| 5   | 100 | 94  | 90  | 87  | 99  | 93  | 89  | 86  | 92  | 88  | 85  |  | 90  | 87  | 85  |  | 89  |
| 6   | 97  | 91  | 86  | 83  | 96  | 90  | 86  | 83  | 89  | 85  | 82  |  | 87  | 84  | 82  |  | 86  |
| 7   | 94  | 87  | 83  | 80  | 93  | 87  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 79  |  | 84  |
| 8   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  |  | 82  | 79  | 76  |  | 81  |
| 9   | 89  | 82  | 77  | 74  | 88  | 81  | 77  | 74  | 80  | 77  | 74  |  | 80  | 76  | 74  |  | 79  |
| 10  | 86  | 79  | 75  | 72  | 85  | 79  | 75  | 72  | 78  | 74  | 72  |  | 77  | 74  | 72  |  | 77  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 148014 |
| 5°  | 145014 |
| 10° | 134890 |
| 15° | 98911  |
| 20° | 50638  |
| 25° | 18243  |
| 30° | 7115   |
| 35° | 2490   |
| 40° | 1031   |
| 45° | 279    |
| 50° | 239    |
| 55° | 268    |
| 60° | 219    |
| 65° | 208    |
| 70° | 256    |
| 75° | 339    |
| 80° | 253    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 339 cd/sqm

TEST NUMBER: P1273006

CATALOG NUMBER: P3A02R359830DE010 E3CB1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 61.4   | 27.0      |
| 10°-20°   | 115.2  | 50.8      |
| 20°-30°   | 40.8   | 18.0      |
| 30°-40°   | 7.2    | 3.2       |
| 40°-50°   | 1.0    | 0.5       |
| 50°-60°   | 0.6    | 0.2       |
| 60°-70°   | 0.4    | 0.2       |
| 70°-80°   | 0.3    | 0.2       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 217.4  | 95.8      |
| 0°-40°    | 224.6  | 98.9      |
| 0°-60°    | 226.2  | 99.6      |
| 0°-90°    | 227.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 227.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 675 |      |
| 5°  | 659 | 61   |
| 15° | 436 | 115  |
| 25° | 75  | 41   |
| 35° | 9   | 7    |
| 45° | 1   | 1    |
| 55° | 1   | 1    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1273006

CATALOG NUMBER: P3A02R359830DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 675.0 |
| 1°    | 674.8 |
| 2°    | 672.7 |
| 3°    | 668.6 |
| 4°    | 664.8 |
| 5°    | 658.8 |
| 6°    | 652.5 |
| 7°    | 645.5 |
| 8°    | 636.9 |
| 9°    | 623.5 |
| 10°   | 605.8 |
| 11°   | 581.3 |
| 12°   | 551.9 |
| 13°   | 516.8 |
| 14°   | 478.2 |
| 15°   | 435.7 |
| 17.5° | 324.5 |
| 20°   | 217.0 |
| 22.5° | 130.9 |
| 25°   | 75.4  |
| 27.5° | 45.0  |
| 30°   | 28.1  |
| 32.5° | 16.3  |
| 35°   | 9.3   |
| 37.5° | 5.9   |
| 40°   | 3.6   |
| 42.5° | 1.8   |
| 45°   | 0.9   |
| 47.5° | 0.7   |
| 50°   | 0.7   |
| 52.5° | 0.7   |
| 55°   | 0.7   |
| 57.5° | 0.5   |
| 60°   | 0.5   |
| 62.5° | 0.5   |
| 65°   | 0.4   |
| 67.5° | 0.4   |
| 70°   | 0.4   |
| 72.5° | 0.4   |
| 75°   | 0.4   |
| 77.5° | 0.2   |
| 80°   | 0.2   |
| 82.5° | 0.2   |
| 85°   | 0.0   |
| 87.5° | 0.0   |



TEST NUMBER: P1273006

CATALOG NUMBER: P3A02R359830DE010 E3CB1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)