

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273109

Luminaire Tested: P3A02R509830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R509830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 65.0 lumens
Efficiency: N/A
Efficacy: 18.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273109

CATALOG NUMBER: P3A02R509830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273109

CATALOG NUMBER: P3A02R509830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	76	73	70	68		
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60		
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56		
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18902
5°	18402
10°	16967
15°	14915
20°	12484
25°	9896
30°	7267
35°	5006
40°	3177
45°	1768
50°	955
55°	803
60°	702
65°	623
70°	577
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1768 cd/sqm

TEST NUMBER: P1273109

CATALOG NUMBER: P3A02R509830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.7	11.9
10°-20°	18.2	28.0
20°-30°	18.6	28.6
30°-40°	11.8	18.2
40°-50°	4.7	7.2
50°-60°	1.9	2.9
60°-70°	1.2	1.9
70°-80°	0.6	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	44.6	68.5
0°-40°	56.4	86.7
0°-60°	63.0	96.8
0°-90°	65.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	65.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	86	
5°	84	8
15°	66	18
25°	41	19
35°	19	12
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273109

CATALOG NUMBER: P3A02R509830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	86.2
2.5°	85.6
5°	83.6
7.5°	80.4
10°	76.2
12.5°	71.2
15°	65.7
17.5°	59.7
20°	53.5
22.5°	47.2
25°	40.9
27.5°	34.6
30°	28.7
32.5°	23.4
35°	18.7
37.5°	14.6
40°	11.1
42.5°	8.2
45°	5.7
47.5°	3.9
50°	2.8
52.5°	2.4
55°	2.1
57.5°	1.8
60°	1.6
62.5°	1.4
65°	1.2
67.5°	1.1
70°	0.9
72.5°	0.7
75°	0.6
77.5°	0.4
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)