

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426587

Luminaire Tested: P3A13RH9827DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RH9827DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 2700K CCT AND, 98CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 324.0 lumens
Efficiency: N/A
Efficacy: 22.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426587

CATALOG NUMBER: P3A13RH9827DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426587

CATALOG NUMBER: P3A13RH9827DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156237
5°	143143
10°	125092
15°	109717
20°	55538
25°	27631
30°	24991
35°	19006
40°	13339
45°	9024
50°	5765
55°	3861
60°	2675
65°	2127
70°	1282
75°	1186
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9024 cd/sqm

TEST NUMBER: P1426587

CATALOG NUMBER: P3A13RH9827DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.2	18.3
10°-20°	122.5	37.8
20°-30°	59.7	18.4
30°-40°	44.6	13.8
40°-50°	23.0	7.1
50°-60°	9.4	2.9
60°-70°	3.8	1.2
70°-80°	1.4	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.4	74.5
0°-40°	286.0	88.3
0°-60°	318.4	98.3
0°-90°	324.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	324.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	712	
5°	650	59
15°	483	122
25°	114	60
35°	71	45
45°	29	23
55°	10	9
65°	4	4
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1426587

CATALOG NUMBER: P3A13RH9827DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	712.5
2.5°	696.3
5°	650.3
7.5°	601.0
10°	561.8
12.5°	532.7
15°	483.3
17.5°	377.2
20°	238.0
22.5°	141.3
25°	114.2
27.5°	105.5
30°	98.7
32.5°	86.5
35°	71.0
37.5°	58.1
40°	46.6
42.5°	37.2
45°	29.1
47.5°	22.3
50°	16.9
52.5°	12.8
55°	10.1
57.5°	8.1
60°	6.1
62.5°	4.7
65°	4.1
67.5°	2.7
70°	2.0
72.5°	2.0
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)