

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273113

Luminaire Tested: P3A02R509830DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R509830DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 201.0 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273113

CATALOG NUMBER: P3A02R509830DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1273113

CATALOG NUMBER: P3A02R509830DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	84		88	85	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	80	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	75	71		88	80	74	70		78	73	70		77	73	69		75	72	69
7	85	76	70	66		84	75	70	66		74	69	66		73	69	65		72	68	65
8	81	72	66	62		80	71	66	62		70	65	62		69	65	62		68	64	61
9	78	68	63	59		76	68	62	59		67	62	59		66	62	58		65	61	58
10	74	65	59	56		73	65	59	56		64	59	55		63	58	55		62	58	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63986
5°	62712
10°	58739
15°	52577
20°	44244
25°	33776
30°	21953
35°	13010
40°	7528
45°	3783
50°	1399
55°	1109
60°	1009
65°	934
70°	898
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3783 cd/sqm

TEST NUMBER: P1273113

CATALOG NUMBER: P3A02R509830DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	13.2
10°-20°	64.1	31.9
20°-30°	62.8	31.3
30°-40°	31.7	15.7
40°-50°	10.0	5.0
50°-60°	2.6	1.3
60°-70°	1.8	0.9
70°-80°	1.1	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	153.4	76.3
0°-40°	185.1	92.1
0°-60°	197.7	98.3
0°-90°	201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	292	
5°	285	27
15°	232	64
25°	140	63
35°	49	32
45°	12	10
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273113

CATALOG NUMBER: P3A02R509830DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	291.8
2.5°	290.1
5°	284.9
7.5°	275.6
10°	263.8
12.5°	248.6
15°	231.6
17.5°	212.0
20°	189.6
22.5°	165.5
25°	139.6
27.5°	112.1
30°	86.7
32.5°	65.2
35°	48.6
37.5°	35.9
40°	26.3
42.5°	18.6
45°	12.2
47.5°	7.0
50°	4.1
52.5°	3.0
55°	2.9
57.5°	2.5
60°	2.3
62.5°	2.1
65°	1.8
67.5°	1.6
70°	1.4
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)