

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273136

Luminaire Tested: P3A02R559830DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273136  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R559830DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 151.0 lumens  
Efficiency: N/A  
Efficacy: 41.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273136  
CATALOG NUMBER: P3A02R559830DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1273136  
 CATALOG NUMBER: P3A02R559830DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	54	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	28397
5°	28021
10°	26920
15°	25176
20°	22962
25°	20493
30°	17927
35°	14884
40°	11736
45°	7970
50°	4878
55°	2523
60°	2368
65°	2231
70°	2052
75°	1779
80°	1768
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7970 cd/sqm



TEST NUMBER: P1273136  
 CATALOG NUMBER: P3A02R559830DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	11.9	7.9
10°-20°	31.0	20.5
20°-30°	38.8	25.7
30°-40°	34.7	22.9
40°-50°	20.3	13.4
50°-60°	7.0	4.7
60°-70°	4.2	2.8
70°-80°	2.3	1.6
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	81.8	54.1
0°-40°	116.4	77.1
0°-60°	143.8	95.2
0°-90°	151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	151.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	130	
5°	127	12
15°	111	31
25°	85	39
35°	56	35
45°	26	20
55°	7	7
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1273136  
CATALOG NUMBER: P3A02R559830DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	129.5
2.5°	128.8
5°	127.3
7.5°	124.5
10°	120.9
12.5°	116.5
15°	110.9
17.5°	105.0
20°	98.4
22.5°	91.7
25°	84.7
27.5°	77.8
30°	70.8
32.5°	63.3
35°	55.6
37.5°	48.2
40°	41.0
42.5°	33.4
45°	25.7
47.5°	19.6
50°	14.3
52.5°	9.3
55°	6.6
57.5°	5.9
60°	5.4
62.5°	4.8
65°	4.3
67.5°	3.7
70°	3.2
72.5°	2.7
75°	2.1
77.5°	1.8
80°	1.4
82.5°	0.9
85°	0.5
87.5°	0.4
90°	0.0

(END OF REPORT)