

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273150

Luminaire Tested: P3A02R609830DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R609830DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 214.0 lumens
Efficiency: N/A
Efficacy: 59.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273150
CATALOG NUMBER: P3A02R609830DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1273150
 CATALOG NUMBER: P3A02R609830DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56070
5°	52938
10°	51547
15°	50375
20°	46834
25°	41881
30°	31980
35°	18471
40°	7156
45°	2977
50°	648
55°	115
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2977 cd/sqm



TEST NUMBER: P1273150
 CATALOG NUMBER: P3A02R609830DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.7	10.6
10°-20°	61.8	28.9
20°-30°	77.4	36.2
30°-40°	43.3	20.2
40°-50°	8.2	3.8
50°-60°	0.4	0.2
60°-70°	0.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.9	75.7
0°-40°	205.2	95.9
0°-60°	213.8	99.9
0°-90°	214.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	214.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	256	
5°	240	23
15°	222	62
25°	173	77
35°	69	43
45°	10	8
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1273150
CATALOG NUMBER: P3A02R609830DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	255.7
1°	254.7
2°	251.3
3°	247.4
4°	243.7
5°	240.5
6°	238.0
7°	235.9
8°	234.3
9°	232.9
10°	231.5
11°	230.2
12°	228.7
13°	226.9
14°	224.7
15°	221.9
16°	218.5
17°	214.6
18°	210.3
19°	205.3
20°	200.7
21°	195.8
22°	190.7
23°	185.4
24°	179.5
25°	173.1
26°	165.5
27°	157.0
28°	147.4
29°	137.3
30°	126.3
31°	115.3
32°	103.9
32.5°	97.7
33°	92.1
34°	80.4
35°	69.0
36°	58.7
37°	47.7
37.5°	42.7
38°	37.8
39°	30.5
40°	25.0
42.5°	15.2
45°	9.6



TEST NUMBER: P1273150
CATALOG NUMBER: P3A02R609830DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.3
50°	1.9
52.5°	0.4
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)