

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273168

Luminaire Tested: P3A02R609830DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R609830DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 130.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273168
CATALOG NUMBER: P3A02R609830DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1273168
 CATALOG NUMBER: P3A02R609830DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32936
5°	32203
10°	30149
15°	27060
20°	23265
25°	19235
30°	15192
35°	11297
40°	7786
45°	4869
50°	2695
55°	1567
60°	1403
65°	1193
70°	1026
75°	1101
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4869 cd/sqm



TEST NUMBER: P1273168
 CATALOG NUMBER: P3A02R609830DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.6	10.5
10°-20°	33.1	25.5
20°-30°	36.3	27.9
30°-40°	26.5	20.3
40°-50°	12.5	9.6
50°-60°	4.1	3.2
60°-70°	2.3	1.8
70°-80°	1.3	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	83.0	63.8
0°-40°	109.5	84.2
0°-60°	126.1	96.9
0°-90°	130.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	130.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	150	
5°	146	14
15°	119	33
25°	80	36
35°	42	26
45°	16	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1273168
CATALOG NUMBER: P3A02R609830DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	150.2
2.5°	149.4
5°	146.3
7.5°	141.7
10°	135.4
12.5°	127.9
15°	119.2
17.5°	109.7
20°	99.7
22.5°	89.5
25°	79.5
27.5°	69.5
30°	60.0
32.5°	50.9
35°	42.2
37.5°	34.3
40°	27.2
42.5°	20.9
45°	15.7
47.5°	11.4
50°	7.9
52.5°	5.2
55°	4.1
57.5°	3.6
60°	3.2
62.5°	2.7
65°	2.3
67.5°	2.0
70°	1.6
72.5°	1.4
75°	1.3
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)