

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273305

Luminaire Tested: P3A05R259830DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R259830DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 297.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273305

CATALOG NUMBER: P3A05R259830DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1273305

CATALOG NUMBER: P3A05R259830DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70586
5°	68897
10°	63838
15°	56868
20°	48864
25°	41543
30°	34182
35°	26635
40°	19179
45°	12156
50°	7198
55°	4932
60°	4561
65°	4203
70°	3783
75°	3474
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12156 cd/sqm

TEST NUMBER: P1273305

CATALOG NUMBER: P3A05R259830DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	9.8
10°-20°	69.5	23.4
20°-30°	78.6	26.5
30°-40°	62.2	20.9
40°-50°	31.4	10.6
50°-60°	12.6	4.2
60°-70°	8.0	2.7
70°-80°	4.4	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.1	59.7
0°-40°	239.3	80.6
0°-60°	283.2	95.4
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	322	
5°	313	29
15°	250	70
25°	172	79
35°	100	62
45°	39	31
55°	13	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1273305

CATALOG NUMBER: P3A05R259830DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):


0°	
0°	321.9
1°	321.9
2°	320.8
3°	318.9
4°	316.3
5°	313.0
6°	308.9
7°	304.1
8°	299.0
9°	293.0
10°	286.7
11°	279.7
12°	273.1
13°	265.3
14°	257.9
15°	250.5
17.5°	229.8
20°	209.4
22.5°	190.2
25°	171.7
27.5°	153.5
30°	135.0
32.5°	117.7
35°	99.5
37.5°	82.9
40°	67.0
42.5°	52.2
45°	39.2
47.5°	29.2
50°	21.1
52.5°	15.9
55°	12.9
57.5°	11.8
60°	10.4
62.5°	9.2
65°	8.1
67.5°	7.0
70°	5.9
72.5°	5.2
75°	4.1
77.5°	3.3
80°	2.6
82.5°	1.8
85°	1.1
87.5°	0.4



TEST NUMBER: P1273305

CATALOG NUMBER: P3A05R259830DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)