

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273498

Luminaire Tested: P3A05R609830DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273498  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R609830DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 444.0 lumens  
Efficiency: N/A  
Efficacy: 61.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273498  
CATALOG NUMBER: P3A05R609830DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1273498  
 CATALOG NUMBER: P3A05R609830DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67			
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	116328
5°	109817
10°	106968
15°	104518
20°	97192
25°	86884
30°	66365
35°	38307
40°	14856
45°	6202
50°	1365
55°	191
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6202 cd/sqm



TEST NUMBER: P1273498  
 CATALOG NUMBER: P3A05R609830DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.1	10.6
10°-20°	128.3	28.9
20°-30°	160.6	36.2
30°-40°	89.8	20.2
40°-50°	17.1	3.8
50°-60°	0.9	0.2
60°-70°	0.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.0	75.7
0°-40°	425.8	95.9
0°-60°	443.7	99.9
0°-90°	444.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	444.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	530	
5°	499	47
15°	460	128
25°	359	161
35°	143	90
45°	20	17
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1273498  
CATALOG NUMBER: P3A05R609830DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	530.5
1°	528.3
2°	521.4
3°	513.3
4°	505.6
5°	498.9
6°	493.8
7°	489.5
8°	486.2
9°	483.1
10°	480.4
11°	477.7
12°	474.6
13°	470.8
14°	466.2
15°	460.4
16°	453.3
17°	445.3
18°	436.3
19°	425.9
20°	416.5
21°	406.3
22°	395.8
23°	384.7
24°	372.5
25°	359.1
26°	343.3
27°	325.7
28°	305.9
29°	284.8
30°	262.1
31°	239.2
32°	215.6
32.5°	202.7
33°	191.1
34°	166.9
35°	143.1
36°	121.7
37°	99.0
37.5°	88.6
38°	78.5
39°	63.2
40°	51.9
42.5°	31.6
45°	20.0



TEST NUMBER: P1273498  
CATALOG NUMBER: P3A05R609830DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	11.1
50°	4.0
52.5°	0.9
55°	0.5
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)