

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273562

Luminaire Tested: P3A05R709830DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1273562  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R709830DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 266.0 lumens  
Efficiency: N/A  
Efficacy: 36.9 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273562

CATALOG NUMBER: P3A05R709830DE010 E3DL1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1273562

CATALOG NUMBER: P3A05R709830DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 106 | 101 | 97  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  |  | 93  | 90  | 88  |  | 90  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 83  | 89  | 85  | 81  |  | 87  | 83  | 80  |  | 84  |
| 4   | 95  | 86  | 80  | 76  | 93  | 85  | 80  | 75  | 83  | 78  | 74  |  | 81  | 77  | 73  |  | 79  |
| 5   | 89  | 80  | 74  | 69  | 88  | 79  | 73  | 69  | 78  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 6   | 85  | 75  | 68  | 64  | 83  | 74  | 68  | 64  | 73  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 7   | 80  | 70  | 64  | 59  | 79  | 69  | 63  | 59  | 68  | 62  | 58  |  | 67  | 62  | 58  |  | 66  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  |  | 63  | 58  | 54  |  | 62  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  |
| 10  | 69  | 58  | 52  | 48  | 67  | 58  | 52  | 48  | 57  | 51  | 48  |  | 56  | 51  | 48  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 62385 |
| 5°  | 61237 |
| 10° | 57759 |
| 15° | 52418 |
| 20° | 45854 |
| 25° | 38664 |
| 30° | 31676 |
| 35° | 24574 |
| 40° | 17576 |
| 45° | 11133 |
| 50° | 5561  |
| 55° | 3403  |
| 60° | 2938  |
| 65° | 2698  |
| 70° | 2372  |
| 75° | 2203  |
| 80° | 1894  |
| 85° | 1761  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11133 cd/sqm

TEST NUMBER: P1273562

CATALOG NUMBER: P3A05R709830DE010 E3DL1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 26.0   | 9.8       |
| 10°-20°   | 64.2   | 24.1      |
| 20°-30°   | 73.2   | 27.5      |
| 30°-40°   | 57.2   | 21.5      |
| 40°-50°   | 28.1   | 10.6      |
| 50°-60°   | 8.7    | 3.3       |
| 60°-70°   | 5.1    | 1.9       |
| 70°-80°   | 2.7    | 1.0       |
| 80°-90°   | 0.8    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 163.4  | 61.4      |
| 0°-40°    | 220.6  | 82.9      |
| 0°-60°    | 257.4  | 96.7      |
| 0°-90°    | 266.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 266.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 284 |      |
| 5°  | 278 | 26   |
| 15° | 231 | 64   |
| 25° | 160 | 73   |
| 35° | 92  | 57   |
| 45° | 36  | 28   |
| 55° | 9   | 9    |
| 65° | 5   | 5    |
| 75° | 3   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1273562

CATALOG NUMBER: P3A05R709830DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 284.5 |
| 2.5°  | 283.1 |
| 5°    | 278.2 |
| 7.5°  | 270.5 |
| 10°   | 259.4 |
| 12.5° | 246.4 |
| 15°   | 230.9 |
| 17.5° | 214.2 |
| 20°   | 196.5 |
| 22.5° | 178.0 |
| 25°   | 159.8 |
| 27.5° | 142.1 |
| 30°   | 125.1 |
| 32.5° | 108.0 |
| 35°   | 91.8  |
| 37.5° | 76.2  |
| 40°   | 61.4  |
| 42.5° | 47.7  |
| 45°   | 35.9  |
| 47.5° | 25.2  |
| 50°   | 16.3  |
| 52.5° | 10.7  |
| 55°   | 8.9   |
| 57.5° | 7.8   |
| 60°   | 6.7   |
| 62.5° | 5.9   |
| 65°   | 5.2   |
| 67.5° | 4.4   |
| 70°   | 3.7   |
| 72.5° | 3.0   |
| 75°   | 2.6   |
| 77.5° | 2.2   |
| 80°   | 1.5   |
| 82.5° | 1.1   |
| 85°   | 0.7   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)