

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273654

Luminaire Tested: P3A09R259830DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R259830DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 351.0 lumens
Efficiency: N/A
Efficacy: 31.9 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273654

CATALOG NUMBER: P3A09R259830DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1273654

CATALOG NUMBER: P3A09R259830DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127424
5°	122254
10°	107101
15°	86084
20°	66156
25°	50035
30°	36157
35°	24012
40°	14570
45°	8497
50°	5424
55°	4396
60°	3859
65°	3424
70°	2821
75°	2796
80°	2020
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8497 cd/sqm

TEST NUMBER: P1273654

CATALOG NUMBER: P3A09R259830DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	14.4
10°-20°	104.9	29.9
20°-30°	94.8	27.0
30°-40°	57.0	16.2
40°-50°	22.6	6.5
50°-60°	10.4	3.0
60°-70°	6.4	1.8
70°-80°	3.4	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.3	71.3
0°-40°	307.2	87.5
0°-60°	340.3	96.9
0°-90°	351.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	351.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	581	
5°	555	51
15°	379	105
25°	207	95
35°	90	57
45°	27	23
55°	12	10
65°	7	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1273654

CATALOG NUMBER: P3A09R259830DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	581.1
1°	581.1
2°	578.4
3°	572.4
4°	564.7
5°	555.4
6°	543.4
7°	529.7
8°	513.8
9°	498.0
10°	481.0
11°	461.3
12°	441.1
13°	420.8
14°	400.6
15°	379.2
17.5°	328.9
20°	283.5
22.5°	242.4
25°	206.8
27.5°	173.5
30°	142.8
32.5°	114.9
35°	89.7
37.5°	68.4
40°	50.9
42.5°	37.2
45°	27.4
47.5°	20.8
50°	15.9
52.5°	13.1
55°	11.5
57.5°	9.8
60°	8.8
62.5°	7.1
65°	6.6
67.5°	5.5
70°	4.4
72.5°	3.8
75°	3.3
77.5°	2.7
80°	1.6
82.5°	1.1
85°	1.1
87.5°	0.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P1273654
CATALOG NUMBER: P3A09R259830DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):



(END OF REPORT)