

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273787

Luminaire Tested: P3A09R509830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R509830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 301.0 lumens
Efficiency: N/A
Efficacy: 27.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273787

CATALOG NUMBER: P3A09R509830DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273787

CATALOG NUMBER: P3A09R509830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	68		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95826
5°	93902
10°	87952
15°	78729
20°	66272
25°	50567
30°	32866
35°	19488
40°	11250
45°	5644
50°	2115
55°	1644
60°	1535
65°	1401
70°	1346
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5644 cd/sqm

TEST NUMBER: P1273787

CATALOG NUMBER: P3A09R509830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.7	13.2
10°-20°	95.9	31.9
20°-30°	94.1	31.3
30°-40°	47.4	15.8
40°-50°	15.0	5.0
50°-60°	3.9	1.3
60°-70°	2.7	0.9
70°-80°	1.7	0.6
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.7	76.3
0°-40°	277.1	92.1
0°-60°	296.0	98.3
0°-90°	301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	301.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	437	
5°	427	40
15°	347	96
25°	209	94
35°	73	47
45°	18	15
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1273787

CATALOG NUMBER: P3A09R509830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	437.0
2.5°	434.4
5°	426.6
7.5°	412.7
10°	395.0
12.5°	372.3
15°	346.8
17.5°	317.4
20°	284.0
22.5°	247.8
25°	209.0
27.5°	167.8
30°	129.8
32.5°	97.7
35°	72.8
37.5°	53.8
40°	39.3
42.5°	27.8
45°	18.2
47.5°	10.4
50°	6.2
52.5°	4.5
55°	4.3
57.5°	3.7
60°	3.5
62.5°	3.2
65°	2.7
67.5°	2.4
70°	2.1
72.5°	1.9
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)