

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273955

Luminaire Tested: P3A13R209830DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273955
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R209830DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 910.1 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273955

CATALOG NUMBER: P3A13R209830DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1273955

CATALOG NUMBER: P3A13R209830DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84
9	95	89	85	83	94	89	85	83	88	85	83	87	84	82	87	84	82
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1380394
5°	1162225
10°	725927
15°	271398
20°	93155
25°	38833
30°	18281
35°	8191
40°	3864
45°	1985
50°	716
55°	153
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1985 cd/sqm

TEST NUMBER: P1273955

CATALOG NUMBER: P3A13R209830DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.1	48.2
10°-20°	361.7	39.7
20°-30°	82.2	9.0
30°-40°	20.9	2.3
40°-50°	5.3	0.6
50°-60°	0.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.9	97.0
0°-40°	903.9	99.3
0°-60°	909.8	100.0
0°-90°	910.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6295	
5°	5280	439
15°	1196	362
25°	160	82
35°	31	21
45°	6	5
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1273955

CATALOG NUMBER: P3A13R209830DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6295.1
1°	6241.7
2°	6084.5
3°	5858.9
4°	5582.1
5°	5280.0
6°	4943.4
7°	4572.0
8°	4138.6
9°	3709.2
10°	3260.2
11°	2782.3
12°	2305.2
13°	1901.0
14°	1514.6
15°	1195.5
16°	943.6
17°	744.3
18°	598.1
19°	486.4
20°	399.2
21°	333.7
22°	278.6
23°	231.6
24°	193.2
25°	160.5
27.5°	105.0
30°	72.2
32.5°	44.5
35°	30.6
37.5°	19.6
40°	13.5
42.5°	9.3
45°	6.4
47.5°	4.3
50°	2.1
52.5°	1.1
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1273955

CATALOG NUMBER: P3A13R209830DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)