

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274078

Luminaire Tested: P3A13R409830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R409830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 414.0 lumens
Efficiency: N/A
Efficacy: 28.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274078

CATALOG NUMBER: P3A13R409830DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1274078

CATALOG NUMBER: P3A13R409830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		112	109	107	105		105	104	102		102	100	99		98	97	96
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	92	91
3	104	99	94	91		102	97	93	90		95	91	88		92	89	87		90	88	86
4	100	93	88	85		98	92	88	84		90	86	83		88	85	82		86	84	81
5	96	88	83	79		94	88	83	79		86	82	78		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	78	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	68		84	76	71	67		75	70	67		74	70	67		73	69	67
9	82	73	68	64		81	73	68	64		72	67	64		71	67	64		70	66	64
10	78	70	65	62		78	70	65	61		69	64	61		68	64	61		67	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183187
5°	177878
10°	161409
15°	133349
20°	96188
25°	59495
30°	32207
35°	16650
40°	9046
45°	5055
50°	2559
55°	1912
60°	1710
65°	1660
70°	1603
75°	1525
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5055 cd/sqm

TEST NUMBER: P1274078

CATALOG NUMBER: P3A13R409830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	18.0
10°-20°	159.9	38.6
20°-30°	114.1	27.6
30°-40°	42.0	10.2
40°-50°	13.2	3.2
50°-60°	4.6	1.1
60°-70°	3.2	0.8
70°-80°	1.9	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.6	84.2
0°-40°	390.6	94.3
0°-60°	408.4	98.6
0°-90°	414.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	835	
5°	808	74
15°	587	160
25°	246	114
35°	62	42
45°	16	13
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1274078

CATALOG NUMBER: P3A13R409830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	835.4
2.5°	829.0
5°	808.1
7.5°	773.2
10°	724.9
12.5°	663.4
15°	587.4
17.5°	502.1
20°	412.2
22.5°	323.7
25°	245.9
27.5°	180.5
30°	127.2
32.5°	89.2
35°	62.2
37.5°	44.1
40°	31.6
42.5°	22.7
45°	16.3
47.5°	11.0
50°	7.5
52.5°	5.3
55°	5.0
57.5°	4.6
60°	3.9
62.5°	3.6
65°	3.2
67.5°	2.8
70°	2.5
72.5°	2.1
75°	1.8
77.5°	1.4
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)