

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274088

Luminaire Tested: P3A13R409830DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R409830DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 647.9 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274088
CATALOG NUMBER: P3A13R409830DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1274088
 CATALOG NUMBER: P3A13R409830DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.5	9.3
10°-20°	150.1	23.2
20°-30°	173.5	26.8
30°-40°	136.7	21.1
40°-50°	70.2	10.8
50°-60°	26.8	4.1
60°-70°	17.7	2.7
70°-80°	9.6	1.5
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.0	59.3
0°-40°	520.7	80.4
0°-60°	617.7	95.3
0°-90°	647.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	647.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	663	
5°	649	61
15°	539	150
25°	379	173
35°	219	137
45°	91	70
55°	28	27
65°	18	18
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1274088
CATALOG NUMBER: P3A13R409830DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	663.4
2.5°	659.7
5°	648.9
7.5°	630.0
10°	604.6
12.5°	574.9
15°	538.7
17.5°	501.0
20°	460.4
22.5°	419.0
25°	379.2
27.5°	339.3
30°	300.1
32.5°	260.3
35°	218.9
37.5°	180.5
40°	145.7
42.5°	116.0
45°	90.6
47.5°	66.0
50°	44.9
52.5°	32.6
55°	28.3
57.5°	25.4
60°	23.2
62.5°	20.3
65°	18.1
67.5°	15.2
70°	13.0
72.5°	10.9
75°	9.4
77.5°	7.2
80°	5.1
82.5°	4.3
85°	2.2
87.5°	1.4
90°	0.0

(END OF REPORT)