

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426788

Luminaire Tested: P3A17RH9835DE010 E3HY1GPH

Issue Date: 3/9/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1426788  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17RH9835DE010 E3HY1GPH  
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 98CRI , E3HY1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 438.0 lumens  
Efficiency: N/A  
Efficacy: 21.5 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1426788

CATALOG NUMBER: P3A17RH9835DE010 E3HY1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1426788

CATALOG NUMBER: P3A17RH9835DE010 E3HY1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  | 99  | 98  | 96  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 103 | 100 | 102 | 100 | 98  |  | 99  | 98  | 96  |  | 97  | 95  | 94  | 92  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 95  | 98  | 95  | 93  |  | 96  | 94  | 92  |  | 94  | 92  | 90  | 89  |
| 4   | 103 | 98  | 94  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 89  |  | 93  | 90  | 88  |  | 91  | 89  | 87  | 86  |
| 5   | 100 | 94  | 89  | 86  | 99  | 93  | 89  | 86  | 91  | 88  | 85  |  | 90  | 87  | 84  |  | 88  | 86  | 84  | 83  |
| 6   | 97  | 90  | 86  | 83  | 96  | 89  | 85  | 82  | 88  | 84  | 82  |  | 87  | 84  | 81  |  | 86  | 83  | 81  | 80  |
| 7   | 94  | 87  | 82  | 79  | 93  | 86  | 82  | 79  | 85  | 81  | 79  |  | 84  | 81  | 78  |  | 83  | 80  | 78  | 77  |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 79  | 76  |  | 81  | 78  | 76  |  | 81  | 78  | 75  | 74  |
| 9   | 88  | 81  | 77  | 74  | 87  | 81  | 76  | 74  | 80  | 76  | 73  |  | 79  | 76  | 73  |  | 78  | 75  | 73  | 72  |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 77  | 73  | 71  |  | 76  | 73  | 71  | 70  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 297388 |
| 5°  | 271472 |
| 10° | 235244 |
| 15° | 206925 |
| 20° | 90004  |
| 25° | 34478  |
| 30° | 23320  |
| 35° | 7897   |
| 40° | 2462   |
| 45° | 775    |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 775 cd/sqm

TEST NUMBER: P1426788

CATALOG NUMBER: P3A17RH9835DE010 E3HY1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 111.8  | 25.5      |
| 10°-20°   | 224.4  | 51.2      |
| 20°-30°   | 76.1   | 17.4      |
| 30°-40°   | 23.3   | 5.3       |
| 40°-50°   | 2.4    | 0.6       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 412.3  | 94.1      |
| 0°-40°    | 435.6  | 99.4      |
| 0°-60°    | 438.0  | 100.0     |
| 0°-90°    | 438.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 438.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1356 |      |
| 5°  | 1233 | 112  |
| 15° | 912  | 224  |
| 25° | 142  | 76   |
| 35° | 30   | 23   |
| 45° | 2    | 2    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1426788

CATALOG NUMBER: P3A17RH9835DE010 E3HY1GPH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1356.2 |
| 2.5°  | 1326.7 |
| 5°    | 1233.3 |
| 7.5°  | 1130.2 |
| 10°   | 1056.5 |
| 12.5° | 990.1  |
| 15°   | 911.5  |
| 17.5° | 676.9  |
| 20°   | 385.7  |
| 22.5° | 188.0  |
| 25°   | 142.5  |
| 27.5° | 115.5  |
| 30°   | 92.1   |
| 32.5° | 59.0   |
| 35°   | 29.5   |
| 37.5° | 16.0   |
| 40°   | 8.6    |
| 42.5° | 4.9    |
| 45°   | 2.5    |
| 47.5° | 1.2    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)