

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426089

Luminaire Tested: P3A02RH9835DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02RH9835DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 98CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 90.0 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426089

CATALOG NUMBER: P3A02RH9835DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426089

CATALOG NUMBER: P3A02RH9835DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	89	101	96	91	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	76	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	58		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43396
5°	39753
10°	34735
15°	30488
20°	15425
25°	7670
30°	6938
35°	5274
40°	3721
45°	2512
50°	1603
55°	1070
60°	746
65°	571
70°	385
75°	339
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2512 cd/sqm

TEST NUMBER: P1426089

CATALOG NUMBER: P3A02RH9835DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.4	18.3
10°-20°	34.0	37.8
20°-30°	16.6	18.4
30°-40°	12.4	13.8
40°-50°	6.4	7.1
50°-60°	2.6	2.9
60°-70°	1.1	1.2
70°-80°	0.4	0.5
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	67.0	74.5
0°-40°	79.4	88.2
0°-60°	88.5	98.3
0°-90°	90.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	90.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	198	
5°	181	16
15°	134	34
25°	32	17
35°	20	12
45°	8	6
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426089

CATALOG NUMBER: P3A02RH9835DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	197.9
2.5°	193.4
5°	180.6
7.5°	166.9
10°	156.0
12.5°	148.0
15°	134.3
17.5°	104.8
20°	66.1
22.5°	39.2
25°	31.7
27.5°	29.3
30°	27.4
32.5°	24.0
35°	19.7
37.5°	16.1
40°	13.0
42.5°	10.3
45°	8.1
47.5°	6.2
50°	4.7
52.5°	3.6
55°	2.8
57.5°	2.3
60°	1.7
62.5°	1.3
65°	1.1
67.5°	0.8
70°	0.6
72.5°	0.6
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)