

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1336991

Luminaire Tested: P3A05R209835DE010 E3CA301MW

Issue Date: 2/13/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1336991  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-60)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/13/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R209835DE010 E3CA301MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3CA301MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 426.0 lumens  
Efficiency: N/A  
Efficacy: 59.2 lumens/watt  
Spacing Criteria (0/90/45): 2.3 / 0.53 / 1.19  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1336991

CATALOG NUMBER: P3A05R209835DE010 E3CA301MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1336991

CATALOG NUMBER: P3A05R209835DE010 E3CA301MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 92  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 83  |    |    |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 75  |    |    |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 76  | 71  | 79  | 74  | 71  | 77  | 73  | 70  | 68  |    |    |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 70  | 65  | 74  | 69  | 64  | 72  | 68  | 64  | 71  | 67  | 63  | 61  |    |    |
| 6   | 81  | 71  | 64  | 59  | 80  | 70  | 63  | 58  | 68  | 62  | 58  | 67  | 62  | 58  | 65  | 61  | 57  | 55  |    |    |
| 7   | 76  | 65  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 52  | 62  | 56  | 52  | 60  | 55  | 52  | 50  |    |    |
| 8   | 71  | 60  | 53  | 48  | 70  | 59  | 52  | 48  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 45  |    |    |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 51  | 46  | 43  | 41  |    |    |
| 10  | 62  | 51  | 44  | 39  | 61  | 50  | 44  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 48  | 42  | 39  | 37  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     | 45°   | 90°  | 135° | 180° |
|-----|--------|-------|------|------|------|
| 0°  | 3223   | 3223  | 3223 | 3223 | 3223 |
| 5°  | 7396   | 5525  | 3060 | 1871 | 1607 |
| 10° | 23313  | 9641  | 2494 | 1024 | 779  |
| 15° | 151079 | 17821 | 1839 | 341  | 91   |
| 20° | 455996 | 30476 | 1260 | 0    | 0    |
| 25° | 677192 | 30776 | 750  | 0    | 0    |
| 30° | 761535 | 23396 | 304  | 0    | 0    |
| 35° | 657077 | 13974 | 214  | 0    | 0    |
| 40° | 378366 | 4752  | 0    | 0    | 0    |
| 45° | 92289  | 1923  | 124  | 0    | 124  |
| 50° | 11087  | 512   | 136  | 136  | 409  |
| 55° | 1491   | 0     | 306  | 306  | 573  |
| 60° | 175    | 0     | 526  | 526  | 833  |
| 65° | 208    | 208   | 778  | 778  | 1193 |
| 70° | 256    | 256   | 962  | 962  | 1218 |
| 75° | 0      | 339   | 1271 | 1017 | 1271 |
| 80° | 0      | 505   | 1515 | 1010 | 1515 |
| 85° | 0      | 1006  | 3019 | 1006 | 1006 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 2.5°

Vertical Angle: 45°

Luminance: 92878 cd/sqm

TEST NUMBER: P1336991

CATALOG NUMBER: P3A05R209835DE010 E3CA301MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 2.0    | 0.5       |
| 10°-20°   | 39.5   | 9.3       |
| 20°-30°   | 172.1  | 40.4      |
| 30°-40°   | 173.3  | 40.7      |
| 40°-50°   | 34.8   | 8.2       |
| 50°-60°   | 1.8    | 0.4       |
| 60°-70°   | 1.1    | 0.3       |
| 70°-80°   | 1.0    | 0.2       |
| 80°-90°   | 0.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 213.5  | 50.1      |
| 0°-40°    | 386.8  | 90.8      |
| 0°-60°    | 423.3  | 99.4      |
| 0°-90°    | 426.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 426.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0°  | 15   | 15  | 15  | 15   | 15   |      |
| 5°  | 34   | 25  | 14  | 8    | 7    | 5    |
| 15° | 666  | 78  | 8   | 2    | 0    | 261  |
| 25° | 2799 | 127 | 3   | 0    | 0    | 1262 |
| 35° | 2455 | 52  | 1   | 0    | 0    | 1460 |
| 45° | 298  | 6   | 0   | 0    | 0    | 324  |
| 55° | 4    | 0   | 1   | 1    | 2    | 7    |
| 65° | 0    | 0   | 2   | 2    | 2    | 0    |
| 75° | 0    | 0   | 2   | 1    | 2    | 0    |
| 85° | 0    | 0   | 1   | 0    | 0    | 0    |
| 90° | 0    | 0   | 0   | 0    | 0    |      |

TEST NUMBER: P1336991

CATALOG NUMBER: P3A05R209835DE010 E3CA301MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 45°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0°    | 14.7   | 14.7   | 14.7   | 14.7   | 14.7   | 14.7   | 14.7   | 14.7   | 14.7   | 14.7   | 14.7  |
| 2.5°  | 22.0   | 22.0   | 21.6   | 21.6   | 21.3   | 21.6   | 20.9   | 21.3   | 21.3   | 20.9   | 18.9  |
| 5°    | 33.6   | 34.4   | 34.0   | 34.0   | 33.6   | 34.0   | 33.2   | 32.5   | 31.7   | 31.7   | 25.1  |
| 7.5°  | 55.3   | 54.9   | 54.1   | 54.5   | 53.3   | 52.6   | 51.8   | 51.4   | 49.1   | 47.9   | 32.9  |
| 10°   | 104.7  | 107.1  | 105.1  | 104.7  | 97.8   | 97.4   | 92.8   | 86.2   | 80.4   | 77.3   | 43.3  |
| 12.5° | 288.3  | 300.7  | 281.4  | 272.1  | 266.7  | 245.8  | 236.9  | 214.1  | 192.1  | 175.5  | 54.9  |
| 15°   | 665.5  | 696.1  | 657.0  | 659.7  | 627.3  | 567.7  | 515.6  | 470.7  | 417.8  | 364.5  | 78.5  |
| 17.5° | 1304.0 | 1279.3 | 1258.0 | 1222.1 | 1156.0 | 1068.6 | 956.2  | 842.1  | 743.6  | 640.4  | 109.4 |
| 20°   | 1954.1 | 1932.0 | 1883.7 | 1805.3 | 1721.0 | 1591.5 | 1457.8 | 1286.6 | 1120.8 | 965.4  | 130.6 |
| 21°   | 2177.8 | 2170.5 | 2091.3 | 2042.9 | 1913.1 | 1789.4 | 1635.2 | 1452.0 | 1265.3 | 1081.4 | 134.1 |
| 22°   | 2377.6 | 2333.6 | 2291.1 | 2219.6 | 2090.5 | 1956.0 | 1784.4 | 1591.5 | 1389.0 | 1184.6 | 134.5 |
| 23°   | 2516.0 | 2495.9 | 2455.7 | 2374.9 | 2246.6 | 2088.6 | 1907.7 | 1705.9 | 1492.6 | 1257.6 | 133.3 |
| 24°   | 2669.1 | 2643.5 | 2584.8 | 2490.5 | 2361.0 | 2204.9 | 1998.5 | 1798.3 | 1566.4 | 1319.1 | 130.2 |
| 25°   | 2798.9 | 2759.1 | 2689.5 | 2587.9 | 2446.4 | 2285.3 | 2077.7 | 1857.8 | 1617.8 | 1360.4 | 127.2 |
| 26°   | 2883.2 | 2861.5 | 2772.2 | 2661.7 | 2510.2 | 2344.0 | 2132.2 | 1903.4 | 1651.1 | 1379.4 | 122.1 |
| 27°   | 2970.9 | 2931.1 | 2843.4 | 2716.2 | 2551.9 | 2382.3 | 2163.1 | 1925.5 | 1662.6 | 1380.1 | 115.9 |
| 28°   | 3021.1 | 2977.9 | 2878.5 | 2744.8 | 2579.0 | 2403.5 | 2180.9 | 1932.4 | 1660.3 | 1368.1 | 108.6 |
| 29°   | 3037.0 | 2982.5 | 2885.5 | 2749.4 | 2585.6 | 2405.1 | 2178.2 | 1922.4 | 1639.8 | 1338.8 | 100.1 |
| 30°   | 3007.6 | 2952.0 | 2860.0 | 2727.4 | 2564.7 | 2385.8 | 2153.1 | 1889.1 | 1603.5 | 1296.7 | 92.4  |
| 31°   | 2943.5 | 2896.3 | 2807.4 | 2674.5 | 2518.3 | 2340.5 | 2096.3 | 1834.6 | 1541.7 | 1240.2 | 83.5  |
| 32°   | 2858.8 | 2812.4 | 2725.1 | 2604.9 | 2446.1 | 2266.7 | 2018.6 | 1749.6 | 1469.0 | 1156.0 | 74.6  |
| 33°   | 2731.7 | 2705.0 | 2626.5 | 2511.8 | 2352.9 | 2161.2 | 1914.3 | 1648.0 | 1365.4 | 1062.4 | 66.9  |
| 34°   | 2603.0 | 2569.3 | 2514.5 | 2388.9 | 2218.0 | 2026.7 | 1778.2 | 1507.7 | 1239.1 | 957.7  | 59.5  |
| 35°   | 2454.6 | 2434.5 | 2348.3 | 2247.8 | 2076.2 | 1880.6 | 1633.7 | 1371.2 | 1091.8 | 841.0  | 52.2  |
| 36°   | 2310.8 | 2279.9 | 2181.7 | 2075.4 | 1908.8 | 1697.4 | 1453.6 | 1207.0 | 964.7  | 731.6  | 44.4  |
| 37°   | 2102.1 | 2054.9 | 1985.0 | 1872.9 | 1678.1 | 1498.0 | 1275.4 | 1046.6 | 808.1  | 613.3  | 35.9  |
| 38°   | 1856.7 | 1834.6 | 1737.6 | 1624.8 | 1463.6 | 1292.8 | 1072.5 | 878.5  | 666.7  | 512.1  | 27.4  |
| 39°   | 1567.2 | 1566.8 | 1474.0 | 1392.5 | 1234.8 | 1081.0 | 882.3  | 713.1  | 550.4  | 412.4  | 21.3  |
| 40°   | 1321.8 | 1276.2 | 1219.0 | 1116.5 | 995.6  | 864.9  | 691.0  | 558.1  | 427.1  | 332.4  | 16.6  |
| 42.5° | 693.0  | 689.1  | 655.5  | 578.6  | 510.9  | 434.0  | 345.1  | 287.5  | 224.9  | 183.2  | 10.4  |
| 45°   | 297.6  | 299.5  | 276.3  | 264.7  | 238.5  | 206.4  | 174.3  | 145.3  | 124.4  | 100.9  | 6.2   |
| 47.5° | 75.4   | 72.3   | 71.5   | 74.2   | 74.2   | 71.9   | 64.5   | 60.7   | 56.0   | 51.4   | 3.5   |
| 50°   | 32.5   | 31.7   | 30.9   | 30.9   | 29.0   | 27.8   | 25.9   | 23.6   | 21.6   | 19.3   | 1.5   |
| 52.5° | 12.0   | 12.4   | 12.8   | 12.4   | 12.4   | 12.0   | 12.0   | 11.6   | 10.4   | 9.3    | 0.8   |
| 55°   | 3.9    | 3.9    | 3.9    | 4.3    | 4.3    | 4.6    | 4.6    | 4.6    | 4.6    | 4.3    | 0.0   |
| 57.5° | 0.8    | 0.8    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.5    | 1.5    | 0.0   |
| 60°   | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.0    | 0.0    | 0.0    | 0.0   |
| 62.5° | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4   |
| 65°   | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4   |
| 67.5° | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4   |
| 70°   | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4   |
| 72.5° | 0.4    | 0.0    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4   |
| 75°   | 0.0    | 0.0    | 0.0    | 0.4    | 0.0    | 0.4    | 0.4    | 0.0    | 0.4    | 0.4    | 0.4   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.4    | 0.4   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.4   |



TEST NUMBER: P1336991

CATALOG NUMBER: P3A05R209835DE010 E3CA301MW

**CANDELA DISTRIBUTION (continued):**

|       | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 45° |
|-------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 82.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.4 |
| 85°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.4 |
| 87.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.4 |
| 90°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

TEST NUMBER: P1336991

CATALOG NUMBER: P3A05R209835DE010 E3CA301MW

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90°  | 112.5° | 135° | 157.5° | 180° |
|-------|-------|------|--------|------|--------|------|
| 0°    | 14.7  | 14.7 | 14.7   | 14.7 | 14.7   | 14.7 |
| 2.5°  | 17.0  | 15.1 | 12.8   | 10.8 | 10.4   | 10.0 |
| 5°    | 18.9  | 13.9 | 10.4   | 8.5  | 7.7    | 7.3  |
| 7.5°  | 20.5  | 12.8 | 8.5    | 6.2  | 5.4    | 5.0  |
| 10°   | 21.3  | 11.2 | 7.0    | 4.6  | 3.5    | 3.5  |
| 12.5° | 21.6  | 9.7  | 5.0    | 3.1  | 1.9    | 1.9  |
| 15°   | 21.3  | 8.1  | 3.9    | 1.5  | 0.4    | 0.4  |
| 17.5° | 19.3  | 6.6  | 2.3    | 0.4  | 0.0    | 0.0  |
| 20°   | 16.6  | 5.4  | 1.5    | 0.0  | 0.0    | 0.0  |
| 21°   | 15.8  | 4.6  | 1.2    | 0.0  | 0.0    | 0.0  |
| 22°   | 14.7  | 4.3  | 0.8    | 0.0  | 0.0    | 0.0  |
| 23°   | 13.5  | 3.9  | 0.8    | 0.0  | 0.0    | 0.0  |
| 24°   | 12.4  | 3.5  | 0.4    | 0.0  | 0.0    | 0.0  |
| 25°   | 11.6  | 3.1  | 0.4    | 0.0  | 0.0    | 0.0  |
| 26°   | 10.8  | 2.7  | 0.4    | 0.0  | 0.0    | 0.0  |
| 27°   | 9.7   | 2.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 28°   | 8.9   | 1.9  | 0.0    | 0.0  | 0.0    | 0.0  |
| 29°   | 7.7   | 1.5  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°   | 6.6   | 1.2  | 0.0    | 0.0  | 0.0    | 0.0  |
| 31°   | 5.4   | 1.2  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32°   | 4.6   | 0.8  | 0.0    | 0.0  | 0.0    | 0.0  |
| 33°   | 3.9   | 0.8  | 0.0    | 0.0  | 0.0    | 0.0  |
| 34°   | 3.5   | 0.8  | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°   | 3.1   | 0.8  | 0.0    | 0.0  | 0.0    | 0.0  |
| 36°   | 2.3   | 0.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37°   | 1.9   | 0.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 38°   | 1.5   | 0.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 39°   | 1.2   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 40°   | 1.2   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.5° | 0.4   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 45°   | 0.0   | 0.4  | 0.0    | 0.0  | 0.4    | 0.4  |
| 47.5° | 0.0   | 0.4  | 0.0    | 0.0  | 0.4    | 0.8  |
| 50°   | 0.0   | 0.4  | 0.4    | 0.4  | 0.8    | 1.2  |
| 52.5° | 0.0   | 0.8  | 0.4    | 0.4  | 1.2    | 1.2  |
| 55°   | 0.4   | 0.8  | 0.4    | 0.8  | 1.5    | 1.5  |
| 57.5° | 0.4   | 0.8  | 0.8    | 1.2  | 1.5    | 1.9  |
| 60°   | 0.8   | 1.2  | 1.2    | 1.2  | 1.9    | 1.9  |
| 62.5° | 0.8   | 1.2  | 1.5    | 1.5  | 1.9    | 2.3  |
| 65°   | 0.8   | 1.5  | 1.5    | 1.5  | 1.9    | 2.3  |
| 67.5° | 1.2   | 1.5  | 1.5    | 1.5  | 1.9    | 2.3  |
| 70°   | 1.2   | 1.5  | 1.5    | 1.5  | 1.9    | 1.9  |
| 72.5° | 1.2   | 1.5  | 1.2    | 1.5  | 1.5    | 1.9  |
| 75°   | 1.2   | 1.5  | 1.2    | 1.2  | 1.5    | 1.5  |
| 77.5° | 0.8   | 1.2  | 1.2    | 0.8  | 1.2    | 1.2  |
| 80°   | 0.8   | 1.2  | 0.8    | 0.8  | 1.2    | 1.2  |





TEST NUMBER: P1336991

CATALOG NUMBER: P3A05R209835DE010 E3CA301MW

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-----|--------|------|--------|------|
| 82.5° | 0.8   | 1.2 | 0.8    | 0.4  | 0.8    | 0.8  |
| 85°   | 0.8   | 1.2 | 0.8    | 0.4  | 0.4    | 0.4  |
| 87.5° | 0.8   | 1.2 | 0.8    | 0.4  | 0.0    | 0.4  |
| 90°   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |

(END OF REPORT)