

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426214

Luminaire Tested: P3A05RH9835DE010 E3HY1LI

Issue Date: 3/9/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1426214  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05RH9835DE010 E3HY1LI  
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 98CRI , E3HY1LI TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 295.0 lumens  
Efficiency: N/A  
Efficacy: 41.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1426214  
CATALOG NUMBER: P3A05RH9835DE010 E3HY1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1426214

CATALOG NUMBER: P3A05RH9835DE010 E3HY1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 98 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96 | 95 |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  | 100 | 98  | 97  | 98  | 96  | 95  | 94  | 93 | 92 |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  | 97  | 95  | 93  | 95  | 93  | 92  | 91  | 90 | 89 |
| 4   | 105 | 99  | 95  | 92  | 103 | 98  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 93  | 91  | 89  | 88  | 87 | 86 |
| 5   | 102 | 96  | 92  | 89  | 100 | 95  | 91  | 88  | 93  | 90  | 88  | 92  | 89  | 87  | 90  | 88  | 86  | 85  | 84 | 83 |
| 6   | 99  | 92  | 88  | 85  | 97  | 92  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 84  | 88  | 86  | 84  | 82  | 81 | 80 |
| 7   | 96  | 89  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 79  | 78 | 77 |
| 8   | 93  | 87  | 83  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 76  | 75 | 74 |
| 9   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  | 82  | 79  | 77  | 81  | 79  | 76  | 73  | 72 | 71 |
| 10  | 88  | 82  | 78  | 75  | 87  | 81  | 77  | 75  | 81  | 77  | 75  | 80  | 77  | 75  | 79  | 76  | 74  | 71  | 70 | 69 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 207571 |
| 5°  | 200858 |
| 10° | 183341 |
| 15° | 156664 |
| 20° | 61465  |
| 25° | 14057  |
| 30° | 6330   |
| 35° | 803    |
| 40° | 0      |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 0 cd/sqm

TEST NUMBER: P1426214  
 CATALOG NUMBER: P3A05RH9835DE010 E3HY1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 83.9   | 28.4      |
| 10°-20°   | 170.0  | 57.6      |
| 20°-30°   | 37.0   | 12.6      |
| 30°-40°   | 4.0    | 1.4       |
| 40°-50°   | 0.0    | 0.0       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 291.0  | 98.6      |
| 0°-40°    | 295.0  | 100.0     |
| 0°-60°    | 295.0  | 100.0     |
| 0°-90°    | 295.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 295.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 947 |      |
| 5°  | 912 | 84   |
| 15° | 690 | 170  |
| 25° | 58  | 37   |
| 35° | 3   | 4    |
| 45° | 0   | 0    |
| 55° | 0   | 0    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1426214

CATALOG NUMBER: P3A05RH9835DE010 E3HY1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 946.6 |
| 2.5°  | 951.6 |
| 5°    | 912.5 |
| 7.5°  | 859.4 |
| 10°   | 823.4 |
| 12.5° | 778.3 |
| 15°   | 690.1 |
| 17.5° | 500.8 |
| 20°   | 263.4 |
| 22.5° | 101.2 |
| 25°   | 58.1  |
| 27.5° | 39.1  |
| 30°   | 25.0  |
| 32.5° | 11.0  |
| 35°   | 3.0   |
| 37.5° | 1.0   |
| 40°   | 0.0   |
| 42.5° | 0.0   |
| 45°   | 0.0   |
| 47.5° | 0.0   |
| 50°   | 0.0   |
| 52.5° | 0.0   |
| 55°   | 0.0   |
| 57.5° | 0.0   |
| 60°   | 0.0   |
| 62.5° | 0.0   |
| 65°   | 0.0   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)