

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273013

Luminaire Tested: P3A02R359830DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R359830DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 188.0 lumens
Efficiency: N/A
Efficacy: 52.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273013
CATALOG NUMBER: P3A02R359830DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1273013

CATALOG NUMBER: P3A02R359830DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90				90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80				80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76				76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73				73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70				70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66				66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	64				64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61				61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94817
5°	91129
10°	79402
15°	60818
20°	40697
25°	24630
30°	14129
35°	7897
40°	4208
45°	2171
50°	1023
55°	803
60°	789
65°	675
70°	705
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2171 cd/sqm



TEST NUMBER: P1273013

CATALOG NUMBER: P3A02R359830DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.7	20.0
10°-20°	73.0	38.8
20°-30°	47.8	25.4
30°-40°	19.4	10.3
40°-50°	5.8	3.1
50°-60°	2.0	1.0
60°-70°	1.3	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.5	84.3
0°-40°	177.8	94.6
0°-60°	185.6	98.7
0°-90°	188.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	188.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	432	
5°	414	38
15°	268	73
25°	102	48
35°	30	19
45°	7	6
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1273013

CATALOG NUMBER: P3A02R359830DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	432.4
1°	431.7
2°	429.7
3°	425.8
4°	421.1
5°	414.0
6°	405.0
7°	395.0
8°	383.8
9°	370.9
10°	356.6
11°	340.7
12°	324.0
13°	305.4
14°	287.7
15°	267.9
17.5°	219.8
20°	174.4
22.5°	134.1
25°	101.8
27.5°	75.8
30°	55.8
32.5°	41.0
35°	29.5
37.5°	20.9
40°	14.7
42.5°	10.2
45°	7.0
47.5°	4.6
50°	3.0
52.5°	2.3
55°	2.1
57.5°	2.0
60°	1.8
62.5°	1.6
65°	1.3
67.5°	1.1
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.5
80°	0.5
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1273013
CATALOG NUMBER: P3A02R359830DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)