

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273069

Luminaire Tested: P3A02R459830DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R459830DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 200.0 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273069

CATALOG NUMBER: P3A02R459830DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1273069

CATALOG NUMBER: P3A02R459830DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		111	109	107	105		105	103	102		101	100	99		98	97	96
2	109	104	100	97		106	102	99	96		99	96	94		96	94	92		93	91	90
3	104	98	93	89		102	96	92	88		94	90	87		91	88	86		89	86	84
4	99	92	87	83		97	91	86	82		89	85	81		87	83	80		85	82	79
5	94	87	81	77		93	86	81	77		84	80	76		82	79	76		81	78	75
6	90	82	76	73		89	81	76	72		80	75	72		78	74	71		77	74	71
7	86	78	72	68		85	77	72	68		76	71	68		75	71	67		74	70	67
8	83	74	68	65		82	73	68	64		72	68	64		71	67	64		70	67	64
9	79	70	65	61		78	70	65	61		69	64	61		68	64	61		67	63	61
10	76	67	62	58		75	67	62	58		66	61	58		65	61	58		65	61	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75104
5°	73343
10°	67422
15°	57140
20°	44314
25°	30994
30°	19522
35°	11484
40°	6498
45°	3163
50°	1092
55°	879
60°	877
65°	830
70°	833
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3163 cd/sqm

TEST NUMBER: P1273069

CATALOG NUMBER: P3A02R459830DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.8	15.4
10°-20°	69.1	34.6
20°-30°	58.7	29.3
30°-40°	28.0	14.0
40°-50°	8.4	4.2
50°-60°	2.1	1.1
60°-70°	1.6	0.8
70°-80°	0.9	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.6	79.3
0°-40°	186.6	93.3
0°-60°	197.2	98.6
0°-90°	200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	200.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	342	
5°	333	31
15°	252	69
25°	128	59
35°	43	28
45°	10	8
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273069

CATALOG NUMBER: P3A02R459830DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	342.5
2.5°	340.4
5°	333.2
7.5°	320.9
10°	302.8
12.5°	278.8
15°	251.7
17.5°	221.4
20°	189.9
22.5°	157.9
25°	128.1
27.5°	100.9
30°	77.1
32.5°	58.0
35°	42.9
37.5°	31.7
40°	22.7
42.5°	15.7
45°	10.2
47.5°	5.7
50°	3.2
52.5°	2.5
55°	2.3
57.5°	2.1
60°	2.0
62.5°	1.8
65°	1.6
67.5°	1.4
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)