

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273211

Luminaire Tested: P3A02R709830DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273211  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R709830DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 213.0 lumens  
Efficiency: N/A  
Efficacy: 59.2 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273211  
CATALOG NUMBER: P3A02R709830DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1273211  
 CATALOG NUMBER: P3A02R709830DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			
4	95	87	81	77	94	86	81	76	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41422
5°	39049
10°	37029
15°	36368
20°	35050
25°	33050
30°	32815
35°	28563
40°	18492
45°	8745
50°	1228
55°	115
60°	88
65°	104
70°	64
75°	85
80°	126
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8745 cd/sqm



TEST NUMBER: P1273211  
 CATALOG NUMBER: P3A02R709830DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	16.6	7.8
10°-20°	45.0	21.1
20°-30°	63.6	29.9
30°-40°	64.0	30.0
40°-50°	23.0	10.8
50°-60°	0.6	0.3
60°-70°	0.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	125.2	58.8
0°-40°	189.1	88.8
0°-60°	212.8	99.9
0°-90°	213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	213.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	189	
5°	177	17
15°	160	45
25°	137	64
35°	107	64
45°	28	23
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1273211  
CATALOG NUMBER: P3A02R709830DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	188.9
1°	188.3
2°	186.7
3°	184.1
4°	180.7
5°	177.4
6°	174.3
7°	171.8
8°	169.6
9°	167.9
10°	166.3
11°	165.0
12°	163.8
13°	162.5
14°	161.4
15°	160.2
16°	158.7
17°	157.1
18°	155.2
19°	152.8
20°	150.2
21°	147.3
22°	144.4
23°	141.6
24°	138.9
25°	136.6
26°	134.9
27°	133.6
28°	132.5
29°	131.3
30°	129.6
31°	127.0
32°	123.4
32.5°	121.4
33°	118.7
34°	113.4
35°	106.7
36°	99.4
37°	91.1
37.5°	87.2
38°	82.0
39°	72.6
40°	64.6
42.5°	44.7
45°	28.2



TEST NUMBER: P1273211  
CATALOG NUMBER: P3A02R709830DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	15.1
50°	3.6
52.5°	0.4
55°	0.3
57.5°	0.3
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.1
77.5°	0.1
80°	0.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)