

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273232

Luminaire Tested: P3A05R159830DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R159830DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 468.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273232
CATALOG NUMBER: P3A05R159830DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1273232
 CATALOG NUMBER: P3A05R159830DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94	94	94	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91	91	91	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89	89	89	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88	88	88	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86	86	86	86
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	85	85	85	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84	84	84	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	909686
5°	762402
10°	359112
15°	108264
20°	40067
25°	15582
30°	5798
35°	1794
40°	630
45°	341
50°	239
55°	268
60°	307
65°	208
70°	256
75°	339
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 341 cd/sqm



TEST NUMBER: P1273232
 CATALOG NUMBER: P3A05R159830DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.8	57.2
10°-20°	159.2	34.0
20°-30°	33.4	7.1
30°-40°	5.4	1.2
40°-50°	0.9	0.2
50°-60°	0.6	0.1
60°-70°	0.4	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.4	98.4
0°-40°	465.8	99.5
0°-60°	467.3	99.9
0°-90°	468.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	468.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4148	
5°	3464	268
15°	477	159
25°	64	33
35°	7	5
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1273232
CATALOG NUMBER: P3A05R159830DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4148.5
1°	4135.5
2°	4069.7
3°	3937.9
4°	3744.8
5°	3463.6
6°	3133.2
7°	2755.4
8°	2394.7
9°	1986.2
10°	1612.8
12.5°	870.2
15°	476.9
17.5°	279.4
20°	171.7
22.5°	105.1
25°	64.4
27.5°	38.9
30°	22.9
32.5°	13.0
35°	6.7
37.5°	3.7
40°	2.2
42.5°	1.5
45°	1.1
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)