

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273419

Luminaire Tested: P3A05R459830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273419
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R459830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 157.0 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273419

CATALOG NUMBER: P3A05R459830DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1273419

CATALOG NUMBER: P3A05R459830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33287
5°	32688
10°	30950
15°	28218
20°	24946
25°	21679
30°	18610
35°	15499
40°	11536
45°	7071
50°	3275
55°	2561
60°	2456
65°	2231
70°	2116
75°	2033
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7071 cd/sqm

TEST NUMBER: P1273419

CATALOG NUMBER: P3A05R459830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.9	8.8
10°-20°	34.6	22.0
20°-30°	41.1	26.2
30°-40°	35.7	22.8
40°-50°	17.9	11.4
50°-60°	6.2	4.0
60°-70°	4.4	2.8
70°-80°	2.4	1.6
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	89.6	57.1
0°-40°	125.3	79.8
0°-60°	149.5	95.2
0°-90°	157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	152	
5°	148	14
15°	124	35
25°	90	41
35°	58	36
45°	23	18
55°	7	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1273419

CATALOG NUMBER: P3A05R459830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	151.8
2.5°	151.1
5°	148.5
7.5°	144.6
10°	139.0
12.5°	132.1
15°	124.3
17.5°	115.6
20°	106.9
22.5°	98.1
25°	89.6
27.5°	81.4
30°	73.5
32.5°	65.9
35°	57.9
37.5°	49.4
40°	40.3
42.5°	31.5
45°	22.8
47.5°	15.0
50°	9.6
52.5°	7.4
55°	6.7
57.5°	6.2
60°	5.6
62.5°	5.1
65°	4.3
67.5°	3.8
70°	3.3
72.5°	2.7
75°	2.4
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.5
87.5°	0.4
90°	0.0

(END OF REPORT)