

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273488

Luminaire Tested: P3A05R559830DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R559830DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 269.0 lumens
Efficiency: N/A
Efficacy: 37.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273488

CATALOG NUMBER: P3A05R559830DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1273488

CATALOG NUMBER: P3A05R559830DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73174
5°	71340
10°	66331
15°	59070
20°	50194
25°	40502
30°	30891
35°	21951
40°	14484
45°	8590
50°	5049
55°	3097
60°	2763
65°	2491
70°	2116
75°	1864
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8590 cd/sqm

TEST NUMBER: P1273488

CATALOG NUMBER: P3A05R559830DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.1	11.2
10°-20°	72.1	26.8
20°-30°	76.4	28.4
30°-40°	51.6	19.2
40°-50°	22.6	8.4
50°-60°	8.1	3.0
60°-70°	4.7	1.8
70°-80°	2.5	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	178.6	66.4
0°-40°	230.2	85.6
0°-60°	260.9	97.0
0°-90°	269.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	269.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	334	
5°	324	30
15°	260	72
25°	167	76
35°	82	52
45°	28	23
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1273488

CATALOG NUMBER: P3A05R559830DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	333.7
2.5°	331.1
5°	324.1
7.5°	312.6
10°	297.9
12.5°	280.1
15°	260.2
17.5°	238.0
20°	215.1
22.5°	191.1
25°	167.4
27.5°	144.1
30°	122.0
32.5°	100.9
35°	82.0
37.5°	65.0
40°	50.6
42.5°	38.1
45°	27.7
47.5°	20.3
50°	14.8
52.5°	10.3
55°	8.1
57.5°	7.4
60°	6.3
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.3
72.5°	3.0
75°	2.2
77.5°	1.8
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)