

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273558

Luminaire Tested: P3A05R709830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R709830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 183.0 lumens
Efficiency: N/A
Efficacy: 25.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273558

CATALOG NUMBER: P3A05R709830DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273558

CATALOG NUMBER: P3A05R709830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35436
5°	34999
10°	34001
15°	32554
20°	30499
25°	27703
30°	23928
35°	19060
40°	13883
45°	9117
50°	4264
55°	1338
60°	1272
65°	1245
70°	1154
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9117 cd/sqm

TEST NUMBER: P1273558

CATALOG NUMBER: P3A05R709830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.0	8.2
10°-20°	40.1	21.9
20°-30°	52.2	28.5
30°-40°	44.3	24.2
40°-50°	22.8	12.5
50°-60°	4.4	2.4
60°-70°	2.4	1.3
70°-80°	1.5	0.8
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	107.3	58.6
0°-40°	151.5	82.8
0°-60°	178.8	97.7
0°-90°	183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	183.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	162	
5°	159	15
15°	143	40
25°	114	52
35°	71	44
45°	29	23
55°	4	4
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1273558

CATALOG NUMBER: P3A05R709830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	161.6
2.5°	161.0
5°	159.0
7.5°	156.1
10°	152.7
12.5°	148.3
15°	143.4
17.5°	137.4
20°	130.7
22.5°	123.0
25°	114.5
27.5°	104.9
30°	94.5
32.5°	83.1
35°	71.2
37.5°	59.6
40°	48.5
42.5°	38.2
45°	29.4
47.5°	21.6
50°	12.5
52.5°	5.5
55°	3.5
57.5°	3.3
60°	2.9
62.5°	2.7
65°	2.4
67.5°	2.2
70°	1.8
72.5°	1.6
75°	1.5
77.5°	1.1
80°	0.9
82.5°	0.5
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)