

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273593

Luminaire Tested: P3A09R159830DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R159830DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 432.0 lumens
Efficiency: N/A
Efficacy: 39.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273593

CATALOG NUMBER: P3A09R159830DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1273593

CATALOG NUMBER: P3A09R159830DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108961
5°	106009
10°	96881
15°	84859
20°	72783
25°	60778
30°	48640
35°	36486
40°	26478
45°	17304
50°	10814
55°	7340
60°	6491
65°	5967
70°	5642
75°	5083
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17304 cd/sqm

TEST NUMBER: P1273593

CATALOG NUMBER: P3A09R159830DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	10.3
10°-20°	104.2	24.1
20°-30°	114.7	26.6
30°-40°	85.9	19.9
40°-50°	44.5	10.3
50°-60°	18.5	4.3
60°-70°	11.5	2.7
70°-80°	6.4	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	263.3	61.0
0°-40°	349.3	80.9
0°-60°	412.3	95.4
0°-90°	432.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	432.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	497	
5°	482	44
15°	374	104
25°	251	115
35°	136	86
45°	56	45
55°	19	18
65°	12	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1273593

CATALOG NUMBER: P3A09R159830DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	496.9
1°	497.5
2°	495.8
3°	492.5
4°	487.6
5°	481.6
6°	473.9
7°	465.7
8°	455.9
9°	445.5
10°	435.1
12.5°	405.0
15°	373.8
17.5°	342.6
20°	311.9
22.5°	280.8
25°	251.2
27.5°	221.6
30°	192.1
32.5°	163.1
35°	136.3
37.5°	113.3
40°	92.5
42.5°	73.3
45°	55.8
47.5°	42.1
50°	31.7
52.5°	23.5
55°	19.2
57.5°	17.0
60°	14.8
62.5°	13.1
65°	11.5
67.5°	9.9
70°	8.8
72.5°	7.1
75°	6.0
77.5°	4.9
80°	3.8
82.5°	2.7
85°	1.6
87.5°	0.5
90°	0.0

(END OF REPORT)