

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273647

Luminaire Tested: P3A09R259830DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273647  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R259830DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 215.0 lumens  
Efficiency: N/A  
Efficacy: 19.5 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273647  
CATALOG NUMBER: P3A09R259830DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1273647

CATALOG NUMBER: P3A09R259830DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	51092
5°	49879
10°	46225
15°	41158
20°	35376
25°	30074
30°	24763
35°	19301
40°	13883
45°	8807
50°	5219
55°	3594
60°	3289
65°	3061
70°	2757
75°	2457
80°	2399
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8807 cd/sqm



TEST NUMBER: P1273647

CATALOG NUMBER: P3A09R259830DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.0	9.8
10°-20°	50.3	23.4
20°-30°	56.9	26.5
30°-40°	45.0	20.9
40°-50°	22.7	10.6
50°-60°	9.1	4.2
60°-70°	5.8	2.7
70°-80°	3.2	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	128.2	59.6
0°-40°	173.2	80.6
0°-60°	205.1	95.4
0°-90°	215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	215.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	233	
5°	227	21
15°	181	50
25°	124	57
35°	72	45
45°	28	23
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1273647

CATALOG NUMBER: P3A09R259830DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	233.0
1°	233.0
2°	232.2
3°	230.9
4°	229.0
5°	226.6
6°	223.7
7°	220.2
8°	216.4
9°	212.1
10°	207.6
11°	202.5
12°	197.7
13°	192.0
14°	186.7
15°	181.3
17.5°	166.3
20°	151.6
22.5°	137.7
25°	124.3
27.5°	111.2
30°	97.8
32.5°	85.2
35°	72.1
37.5°	60.0
40°	48.5
42.5°	37.8
45°	28.4
47.5°	21.2
50°	15.3
52.5°	11.5
55°	9.4
57.5°	8.6
60°	7.5
62.5°	6.7
65°	5.9
67.5°	5.1
70°	4.3
72.5°	3.7
75°	2.9
77.5°	2.4
80°	1.9
82.5°	1.3
85°	0.8
87.5°	0.3



TEST NUMBER: P1273647  
CATALOG NUMBER: P3A09R259830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)