

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273728

Luminaire Tested: P3A09R409830DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R409830DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 766.0 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273728

CATALOG NUMBER: P3A09R409830DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1273728

CATALOG NUMBER: P3A09R409830DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93	91	90	88
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90	88	86	85
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88	85	83	82
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85	82	80	79
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82	79	77	76
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79	76	74	73
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77	74	71	70
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	390451
5°	387628
10°	377481
15°	337187
20°	223576
25°	83763
30°	22409
35°	8754
40°	3149
45°	1489
50°	443
55°	191
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1489 cd/sqm

TEST NUMBER: P1273728

CATALOG NUMBER: P3A09R409830DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.2	21.7
10°-20°	393.6	51.4
20°-30°	178.5	23.3
30°-40°	23.1	3.0
40°-50°	4.0	0.5
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	738.2	96.4
0°-40°	761.4	99.4
0°-60°	765.8	100.0
0°-90°	766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1781	
5°	1761	166
15°	1485	394
25°	346	178
35°	33	23
45°	5	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1273728

CATALOG NUMBER: P3A09R409830DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1780.6
1°	1779.5
2°	1776.8
3°	1772.8
4°	1767.7
5°	1761.0
6°	1753.2
7°	1743.6
8°	1731.8
9°	1715.7
10°	1695.3
11°	1671.4
12°	1639.5
13°	1600.1
14°	1548.6
15°	1485.3
16°	1404.6
17°	1312.6
18°	1202.2
19°	1085.5
20°	958.1
21°	830.8
22°	705.3
23°	580.3
24°	457.5
25°	346.2
26°	256.4
27°	187.7
28°	141.1
29°	109.7
30°	88.5
31°	73.2
32°	61.1
32.5°	55.8
33°	50.4
34°	41.0
35°	32.7
36°	25.7
37°	20.4
37.5°	18.2
38°	16.1
39°	13.4
40°	11.0
42.5°	7.2
45°	4.8

TEST NUMBER: P1273728

CATALOG NUMBER: P3A09R409830DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.9
50°	1.3
52.5°	0.5
55°	0.5
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)