

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273740

Luminaire Tested: P3A09R409830DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R409830DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 488.9 lumens
Efficiency: N/A
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273740
CATALOG NUMBER: P3A09R409830DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1273740
 CATALOG NUMBER: P3A09R409830DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109772
5°	107792
10°	101601
15°	92282
20°	81067
25°	69222
30°	57351
35°	44223
40°	31488
45°	21212
50°	11565
55°	8143
60°	7675
65°	7108
70°	6283
75°	6015
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21212 cd/sqm



TEST NUMBER: P1273740
 CATALOG NUMBER: P3A09R409830DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	9.3
10°-20°	113.2	23.2
20°-30°	130.9	26.8
30°-40°	103.2	21.1
40°-50°	53.0	10.8
50°-60°	20.2	4.1
60°-70°	13.4	2.7
70°-80°	7.3	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.8	59.3
0°-40°	392.9	80.4
0°-60°	466.1	95.3
0°-90°	488.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	501	
5°	490	46
15°	406	113
25°	286	131
35°	165	103
45°	68	53
55°	21	20
65°	14	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1273740
CATALOG NUMBER: P3A09R409830DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	500.6
2.5°	497.9
5°	489.7
7.5°	475.4
10°	456.3
12.5°	433.8
15°	406.5
17.5°	378.0
20°	347.4
22.5°	316.2
25°	286.1
27.5°	256.0
30°	226.5
32.5°	196.4
35°	165.2
37.5°	136.2
40°	110.0
42.5°	87.5
45°	68.4
47.5°	49.8
50°	33.9
52.5°	24.6
55°	21.3
57.5°	19.1
60°	17.5
62.5°	15.3
65°	13.7
67.5°	11.5
70°	9.8
72.5°	8.2
75°	7.1
77.5°	5.5
80°	3.8
82.5°	3.3
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)