

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273788

Luminaire Tested: P3A09R509830DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R509830DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 615.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273788

CATALOG NUMBER: P3A09R509830DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1273788

CATALOG NUMBER: P3A09R509830DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195796
5°	191855
10°	179712
15°	160886
20°	135392
25°	103337
30°	67150
35°	39806
40°	23015
45°	11536
50°	4298
55°	3326
60°	3114
65°	2854
70°	2821
75°	2796
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11536 cd/sqm

TEST NUMBER: P1273788

CATALOG NUMBER: P3A09R509830DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.1	13.2
10°-20°	196.0	31.9
20°-30°	192.3	31.3
30°-40°	96.9	15.7
40°-50°	30.6	5.0
50°-60°	7.9	1.3
60°-70°	5.6	0.9
70°-80°	3.5	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.3	76.3
0°-40°	566.2	92.1
0°-60°	604.8	98.3
0°-90°	615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	893	
5°	872	81
15°	709	196
25°	427	192
35°	149	97
45°	37	31
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1273788

CATALOG NUMBER: P3A09R509830DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	892.9
2.5°	887.5
5°	871.6
7.5°	843.2
10°	807.1
12.5°	760.6
15°	708.7
17.5°	648.5
20°	580.2
22.5°	506.3
25°	427.1
27.5°	342.9
30°	265.2
32.5°	199.6
35°	148.7
37.5°	109.9
40°	80.4
42.5°	56.9
45°	37.2
47.5°	21.3
50°	12.6
52.5°	9.3
55°	8.7
57.5°	7.7
60°	7.1
62.5°	6.6
65°	5.5
67.5°	4.9
70°	4.4
72.5°	3.8
75°	3.3
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)