

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273820

Luminaire Tested: P3A09R559830DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R559830DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 397.9 lumens
Efficiency: N/A
Efficacy: 36.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273820

CATALOG NUMBER: P3A09R559830DE010 E3DL1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1273820

CATALOG NUMBER: P3A09R559830DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79		
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55		
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52		
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108259
5°	105547
10°	98128
15°	87378
20°	74253
25°	59931
30°	45678
35°	32498
40°	21440
45°	12714
50°	7471
55°	4588
60°	4079
65°	3684
70°	3142
75°	2796
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12714 cd/sqm

TEST NUMBER: P1273820

CATALOG NUMBER: P3A09R559830DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.5	11.2
10°-20°	106.7	26.8
20°-30°	113.0	28.4
30°-40°	76.4	19.2
40°-50°	33.5	8.4
50°-60°	12.0	3.0
60°-70°	7.0	1.8
70°-80°	3.7	0.9
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	264.3	66.4
0°-40°	340.6	85.6
0°-60°	386.1	97.0
0°-90°	397.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	397.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	494	
5°	480	45
15°	385	107
25°	248	113
35°	121	76
45°	41	33
55°	12	12
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1273820

CATALOG NUMBER: P3A09R559830DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	493.7
2.5°	489.9
5°	479.5
7.5°	462.6
10°	440.7
12.5°	414.5
15°	384.9
17.5°	352.1
20°	318.2
22.5°	282.7
25°	247.7
27.5°	213.2
30°	180.4
32.5°	149.3
35°	121.4
37.5°	96.2
40°	74.9
42.5°	56.3
45°	41.0
47.5°	30.1
50°	21.9
52.5°	15.3
55°	12.0
57.5°	10.9
60°	9.3
62.5°	8.2
65°	7.1
67.5°	6.0
70°	4.9
72.5°	4.4
75°	3.3
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)