

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273822

Luminaire Tested: P3A09R559830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R559830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 226.9 lumens
Efficiency: N/A
Efficacy: 20.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273822

CATALOG NUMBER: P3A09R559830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273822

CATALOG NUMBER: P3A09R559830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		82
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		68
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		52
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		48
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		45
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42672
5°	42131
10°	40480
15°	37866
20°	34536
25°	30824
30°	26941
35°	22379
40°	17662
45°	11970
50°	7300
55°	3785
60°	3508
65°	3321
70°	3077
75°	2711
80°	2652
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11970 cd/sqm

TEST NUMBER: P1273822

CATALOG NUMBER: P3A09R559830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.0	7.9
10°-20°	46.6	20.5
20°-30°	58.4	25.7
30°-40°	52.1	23.0
40°-50°	30.5	13.4
50°-60°	10.5	4.6
60°-70°	6.3	2.8
70°-80°	3.5	1.6
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	122.9	54.2
0°-40°	175.0	77.1
0°-60°	216.0	95.2
0°-90°	226.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	226.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	195	
5°	191	18
15°	167	47
25°	127	58
35°	84	52
45°	39	30
55°	10	11
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1273822

CATALOG NUMBER: P3A09R559830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	194.6
2.5°	193.6
5°	191.4
7.5°	187.1
10°	181.8
12.5°	175.1
15°	166.8
17.5°	157.9
20°	148.0
22.5°	137.8
25°	127.4
27.5°	116.9
30°	106.4
32.5°	95.2
35°	83.6
37.5°	72.4
40°	61.7
42.5°	50.1
45°	38.6
47.5°	29.5
50°	21.4
52.5°	13.9
55°	9.9
57.5°	8.8
60°	8.0
62.5°	7.2
65°	6.4
67.5°	5.6
70°	4.8
72.5°	4.0
75°	3.2
77.5°	2.7
80°	2.1
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)