

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273903

Luminaire Tested: P3A09R709830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R709830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 269.9 lumens
Efficiency: N/A
Efficacy: 24.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273903

CATALOG NUMBER: P3A09R709830DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1273903

CATALOG NUMBER: P3A09R709830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77			
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70			
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65			
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52277
5°	51640
10°	50144
15°	48037
20°	44991
25°	40865
30°	35297
35°	28134
40°	20496
45°	13459
50°	6311
55°	1950
60°	1886
65°	1816
70°	1731
75°	1779
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13459 cd/sqm

TEST NUMBER: P1273903

CATALOG NUMBER: P3A09R709830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.1	8.2
10°-20°	59.2	21.9
20°-30°	76.9	28.5
30°-40°	65.3	24.2
40°-50°	33.7	12.5
50°-60°	6.5	2.4
60°-70°	3.5	1.3
70°-80°	2.1	0.8
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.2	58.6
0°-40°	223.5	82.8
0°-60°	263.7	97.7
0°-90°	269.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	269.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	238	
5°	235	22
15°	212	59
25°	169	77
35°	105	65
45°	43	34
55°	5	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1273903

CATALOG NUMBER: P3A09R709830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	238.4
2.5°	237.6
5°	234.6
7.5°	230.3
10°	225.2
12.5°	218.8
15°	211.6
17.5°	202.7
20°	192.8
22.5°	181.5
25°	168.9
27.5°	154.7
30°	139.4
32.5°	122.5
35°	105.1
37.5°	87.9
40°	71.6
42.5°	56.3
45°	43.4
47.5°	31.9
50°	18.5
52.5°	8.0
55°	5.1
57.5°	4.8
60°	4.3
62.5°	4.0
65°	3.5
67.5°	3.2
70°	2.7
72.5°	2.4
75°	2.1
77.5°	1.6
80°	1.3
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)